



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GLA250 250 MCM Lay In Connector

Nsi Industries

| | |
|------------------|--|
| Catalog Number | GLA250 |
| Manufacturer | Nsi Industries |
| Description | Lay In Connector 250 MCM - 6 Awg Lay-In Connectors Offer The Ultimate In Flexibility. Excellent For Grounding and Continuous Loop Applications. Made Of 6061T-6 Aluminum Alloy. Electro-Tin Plated For Low Contact Resistance. Suitable For Use With Both Copper and Aluminum Conductors. Rated 600V (2000V Max. Per UL486B). UI 486A/B Listed. Temperature Rating 90 Degrees C. |
| Weight per unit | 0.1800 (lbs/each) |
| Product Category | Large Terminals & Connectors |

Features

| | |
|----------------------|---------------|
| Material | Aluminum |
| Number of Conductors | 1 |
| Poles | 1 |
| Voltage Rating | 600 V |
| Warranty | 1 YEAR |
| Wire Size | 250 MCM-6 AWG |
| Wire Type | Al/Cu |

Material, Color, and Finish

| | |
|--------|----------|
| Color | Aluminum |
| Finish | Aluminum |

Dimensions and Weight

| | |
|------|--------------------------|
| Size | L=2.20 - H=1.70 - W=.800 |
|------|--------------------------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|--|
| Description | 250 MCM LAY IN CONNECTOR |
| extra long description | NSI GLA-250 AL 250 MCM Lay In Conne |
| Features | Lay In Connector 250 MCM - 6 AWG Lay-in connectors offer the ultimate in flexibility. Excellent for grounding and continuous loop applications. Made of 6061T-6 aluminum alloy. Electro-tin plated for low contact resistance. Suitable for use with both copper and aluminum conductors. Rated 600V (2000V max. per UL486B). UL 486A/B Listed. Temperature rating 90 degrees C. |
| Long Description | Lay In Connector 250 MCM - 6 AWG Lay-in connectors offer the ultimate in flexibility. Excellent for grounding and continuous loop applications. Made of 6061T-6 aluminum alloy. Electro-tin plated for low contact resistance. Suitable for use with both copper and aluminum conductors. Rated 600V (2000V max. per UL486B). UL 486A/B Listed. Temperature rating 90 degrees C. |
| Product Type | Al 250 MCM Lay In Connector |
| Special Features | 250 MCM-6 AWG - Dual Rated - 20 Pack |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | NSi |
| GTIN | 00662381001931 |
| Manufacturers Part Number | GLA-250 |
| UPC | 662381001931 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------------|
| Category Description | Comp & Mech Lugs and Butt Splices |
| Type | Aluminum Lay-In Lug |

Packaging

| | |
|-----------------|------|
| Carton | 20 |
| Weight Per each | 0.18 |

Uses, Certifications, and Standards

| | |
|--------------------------|------------------|
| Application | Wire Termination |
| environmental conditions | 90 C |
| standard | cULus |
| Temperature Rating | 90 C |