



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

106 Industrial Drive
71292-0000, LA West Monroe
Phone: 318-398-9757
Fax: 318-398-9704



GMA10A 10A 125V Fa 5X20MM Glass Fuse *Bussmann Fuses*

| | |
|------------------|-------------------------------------|
| Catalog Number | GMA10A |
| Manufacturer | Bussmann Fuses |
| Description | Buss Gma-10A UI Fast Acting 5MM Gla |
| Weight per unit | 0.0040 (lbs/each) |
| Product Category | Tools & Testers |

Features

| | |
|--------------------|---|
| amperage rating | 10 Amp |
| connection | Ferrule End X Ferrule End |
| Response Time | 60 Min Maximum at 135%, 2 Min Maximum at 200% |
| type of indicators | Non-Indicating |
| Voltage Rating | 125 VAC |

Dimensions and Weight

| | |
|------|------------------------------|
| Size | 5 mm Diameter X 20 mm Length |
|------|------------------------------|

Descriptions

| | |
|------------------|---|
| Description | 10A 125V FA 5X20MM GLASS FUSE |
| Long Description | BUSS GMA-10A UL Fast Acting 5mm Gla |
| Product Type | UI Fast Acting 5MM Glass Fuse 10a |
| Special Features | Low Breaking Capacity, Interrupt Rating 200 Amp at 125 Vac, Material Glass Tube, Nickel Plated Brass Endcap |

Manufacturer Information

| | |
|---------------------------|-------------------------------|
| Brand | Cooper Bussmann North America |
| GTIN | 00051712716727 |
| Manufacturers Part Number | GMA-10A |
| UPC | 051712716727 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------------------|
| Category Description | GLASS FUSES (and ceramic) |
| Type | Electronic, Fast Acting |

Availability

| | |
|---------------------|----------|
| Manufacturer Status | Inactive |
| Status | Inactive |

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Package | 5 |
| Weight Per each | 0.004 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

106 Industrial Drive
71292-0000, LA West Monroe
Phone: 318-398-9757
Fax: 318-398-9704

Uses, Certifications, and Standards

| | |
|-------------|---------------------|
| Application | Electronic Circuits |
| standard | UL 248-14, CSA, CE |