



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



F32T8SPP30ECO 32W T8 48" 30K 80CRI 2725 LM

Ge By Current Lamps

Catalog Number	F32T8SPP30ECO
Manufacturer	Ge By Current Lamps
Description	Linear Fluorescent Lamp, Pin/Plug-In G13 Base, T8 Bulb Shape, 80, 30000 H Average Life, 3000 K, 32 W, 2900 LM Brightness (Lumens), Soda Lime Glass Housing Material, 1.0 In Diameter, 48.0 In Length, Instant;Rapid, +10 °C Operating Temperature, 0.56 LB/Ea
Weight per unit	0.5600 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

Base	Medium Bi-Pin (G13)
lumens	2.9k lm

Material, Color, and Finish

color rendering index (cri)	80 C
-----------------------------	------

Descriptions

Description	32W T8 48" 30K 80CRI 2725 LM
-------------	------------------------------

Manufacturer Information

Brand	TUNGSRAM
GTIN	00043168663472
Manufacturers Part Number	F32T8/SPP30/ECO
sub brand	GEÂ®
UPC	043168663472

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
----------------------	-------------

Packaging


Carton	1
Package	36
Weight Per each	0.56



GE
Lighting

66347 - F32T8/SPP30/ECO

F32T8/SPP30/ECO-LFL PULP TRY PK NEW COLOR TEMP



GENERAL CHARACTERISTICS

Lamp Type	Linear Fluorescent - Straight
	Linear
Bulb	T8
Base	Medium Bi-Pin (G13)
Rated Life (NOM)	30000.0 h
Rated Life (instant start) @ Time	21000 h @ 3 h
	30000 h @ 12 h
Rated Life (rapid start) @ Time	30000.0 @ 3.0/36000.0 @ 12.0 h
Bulb Material	Sodalime glass
Starting Temperature (MIN)	10.0 °C
Mercury Content (NOM)	2.95 mg
Picograms of Mercury (NOM)	36.1 pg
Primary Application	Full Wattage

PHOTOMETRIC CHARACTERISTICS

Initial Lumens (NOM)	2900.0
Mean Lumens (NOM)	2725.0
Nominal Initial Lumens per Watt (NOM)	90.625
Color Temperature (NOM)	3000.0 K
Color Rendering Index (CRI) (NOM)	80.0

ELECTRICAL CHARACTERISTICS

Wattage (NOM)	32.0
---------------	------

DIMENSIONS

Maximum Overall Length (MOL) (NOM)	48.000 in(1219.2 mm)
Nominal Length (NOM)	48.000 in(1219.2 mm)
Bulb Diameter (DIA) (NOM)	1.000 in(25.4 mm)

PRODUCT INFORMATION

Product Code	66347
Description	F32T8/SPP30/ECO
Standard Package	Case
Standard Package GTIN	10043168663479
Standard Package Quantity	36
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	36
UPC	043168663472