



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

F60T12CW 50W T12 60" Cool White 62 Cri Single Pin Lamp

Sylvania-Ledvance

Catalog Number	F60T12CW
Manufacturer	Sylvania-Ledvance
Description	
Weight per unit	0.8700 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

average life	12000 Hr
Base	Single Pin
lumens	3.7k lm
Shape	T12
start type	Instant Start
total harmonic distortion	Ballast Dependent
Wattage	50 WTT

Material, Color, and Finish

color rendering index (cri)	60 WTT
color temperature	4200 W
Finish	Phosphor Coated

Dimensions and Weight

Diameter	1.5 in in
----------	-----------

Descriptions

Description	50W T12 60" COOL WHITE 62 CRI SINGLE PIN LAMP
Product Type	F60T12CW 30/CS 1/Sku
Special Features	COOL WHITE

Manufacturer Information

Brand	Sylvania (Usc)
GTIN	00046135260018
Manufacturers Part Number	F60T12/CW/26001
UPC	046135260018

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT

Packaging

Carton	1
Package	30
Weight Per each	0.87

Uses, Certifications, and Standards

Application	COMMERCIAL/RESIDENTIAL
-------------	------------------------

Product Number: 26001

Order Abbreviation: F60T12/CW

General Description: 50W, 60" MOL, T12 instant start Slimline fluorescent lamp, Cool White phosphor, 4200K color temperature, 60 CRI

*** Full Case Required**

Product Information

Abbrev. With Packaging Info.	F60T12CW 30/CS 1/SKU
Actual Length (in)	58.000
Actual Length (mm)	1473.20
Average Rated Life (hr)	12000
Base	Single Pin
Bulb	T12
Color Rendering Index (CRI)	60
Color Temperature/CCT (K)	4200
Diameter (in)	1.593
Diameter (mm)	40.46
Industry Standards	ANSI C78.81 - 2001
Initial Lumens at 25C	3700
Mean Lumens at 25C	3256
Mean Lumens at 35C	3256
Nominal Length (in)	60.000
Nominal Length (mm)	1524.00
Nominal Wattage (W)	50.00

Footnotes

- Approximate initial lumens after 100 hours operation.
- The life ratings of fluorescent lamps are based on 3 hr. operating cycles under specified conditions and with ballast meeting ANSI specifications. If operating cycle is increased, there will be a corresponding increase in the average hours life.
- Minimum starting temperature is a function of the ballast; consult the ballast manufacturer.
- Average life rating at 12 hours operation per start is 18,000 hours.