


Product Number: 25126

Order Abbreviation: F60T12/CW/HO

General Description: 75W, 60" MOL, T12 HO (800 mA) rapid start fluorescent lamp, Cool White phosphor, 4200K color temperature, 60 CRI



*** Full Case Required**

Product Information

Abbrev. With Packaging Info.	F60T12CWHO 30/CS 1/SKU
Actual Length (in)	57.720
Actual Length (mm)	1466.09
Average Rated Life (hr)	12000
Base	Recessed Double Contact
Bulb	T12
Color Rendering Index (CRI)	60
Color Temperature/CCT (K)	4200
Diameter (in)	1.593
Diameter (mm)	40.46
Industry Standards	ANSI C78.81 - 2001
Initial Lumens at 25C	5200
Mean Lumens at 25C	4212
Mean Lumens at 35C	4212
Nominal Length (in)	60.000
Nominal Length (mm)	1524.00
Nominal Wattage (W)	75.00


Footnotes

- Approximate initial lumens after 100 hours operation.
- The life ratings of fluorescent lamps are based on 3 hr. operating cycles under specified conditions and with ballast meeting ANSI specifications. If operating cycle is increased, there will be a corresponding increase in the average hours life.
- Minimum starting temperature is a function of the ballast; consult the ballast manufacturer.
- Average life rating at 12 hours operation per start is 18,000 hours.

Product Number: 25126

Order Abbreviation: F60T12/CW/HO

General Description: 75W, 60" MOL, T12 HO (800 mA) rapid start fluorescent lamp, Cool White phosphor, 4200K color temperature, 60 CRI



*** Full Case Required**

Product Information

Abbrev. With Packaging Info.	F60T12CWHO 30/CS 1/SKU
Actual Length (in)	57.720
Actual Length (mm)	1466.09
Average Rated Life (hr)	12000
Base	Recessed Double Contact
Bulb	T12
Color Rendering Index (CRI)	60
Color Temperature/CCT (K)	4200
Diameter (in)	1.593
Diameter (mm)	40.46
Industry Standards	ANSI C78.81 - 2001
Initial Lumens at 25C	5200
Mean Lumens at 25C	4212
Mean Lumens at 35C	4212
Nominal Length (in)	60.000
Nominal Length (mm)	1524.00
Nominal Wattage (W)	75.00

Footnotes

- Approximate initial lumens after 100 hours operation.
- The life ratings of fluorescent lamps are based on 3 hr. operating cycles under specified conditions and with ballast meeting ANSI specifications. If operating cycle is increased, there will be a corresponding increase in the average hours life.
- Minimum starting temperature is a function of the ballast; consult the ballast manufacturer.
- Average life rating at 12 hours operation per start is 18,000 hours.