

## Device and outlet boxes

Cat. #	Bend radius (in.)	Internal volume (cu. in.)	Cat. #	Bend radius (in.)	Internal volume (cu. in.)	Cat. #	Bend radius (in.)	Internal volume (cu. in.)	Cat. #	Bend radius (in.)	Internal volume (cu. in.)
CPS12021		18.0	FDC1		23.0	FS097		37.5	FSR1		15.8
CPS12022		18.0	FDC2		23.0	FS1		15.8	FSR2		15.8
CPS12026		18.0	FDC3		23.0	FS1 SA		15.8	GRF19		17.8
FD019		24.3	FDL1		23.0	FS2		15.8	GRF39		41.0
FD029		60.3	FDL2		23.0	FS2 SA		15.8	GRFX119		17.8
FD039		95.5	FDR1		23.0	FS3		15.8	GRFX129		27.0
FD062		41.3	FDR2		23.0	FSC1		15.8	GRFX139		41.0
FD063		60.5	FS019		15.8	FSC2		15.8	GRFX219		17.8
FD1		23.0	FS029		40.8	FSC3		15.8	GRFX229		27.0
FD2		23.0	FS039		64.3	FSL1		15.8	GRFX239		27.0
FD3		23.0	FS094		54.8	FSL2		15.8			

## Condulet® outlet boxes

Cat. #	Bend radius (in.)	Internal volume (cu. in.)	Cat. #	Bend radius (in.)	Internal volume (cu. in.)	Cat. #	Bend radius (in.)	Internal volume (cu. in.)	Cat. #	Bend radius (in.)	Internal volume (cu. in.)
EABC16		18.5	GRFX329		27.0	GUAD14		5.0	GUAN36	2.0	15.5
EABC26		20.5	GRFX339		41.0	GUAD16		13.5	GUAN47	2.3	27.5
EABC36		20.5	GRUE19		28.0	GUAD24		5.8	GUAN59	3.6	77.8
EABL16		18.5	GRUE29		28.0	GUAD26		13.5	GUAN69	3.0	80.0
EABL26		20.5	GRUE39		28.0	GUAD36		15.5	GUAP777775		27.3
EABL36		20.5	GUA047		5.8	GUAD49		80.0	GUAT14		5.0
EABT16	1.3	18.5	GUA0631		8.8	GUAG6665		22.8	GUAT16		13.3
EABT26	1.3	20.5	GUA067		14.8	GUAG6775		22.8	GUAT24	0.8	5.8
EABT36	1.1	20.5	GUA0716		40.8	GUAG7665		22.8	GUAT26	1.3	13.5
EABX16		18.5	GUA077		23.5	GUAG7775		22.8	GUAT36	1.1	15.5
EABX26		20.5	GUA14		5.0	GUAG7875		22.8	GUAT37	1.5	27.5
EABX36		20.5	GUA16		13.3	GUAG7885		22.8	GUAT47	1.3	27.5
EABY16		18.5	GUA24		5.8	GUAG8775		22.8	GUAT49	2.0	80.0
EABY26		20.5	GUA26		13.5	GUAG8785		22.8	GUAT59	1.9	79.3
EAJB16		18.5	GUA36		15.5	GUAG8885		22.8	GUAT69	4.0	80.0
EAJB26		20.5	GUA47		27.5	GUAH77775		23.5	GUAW14		5.0
EAJB36		20.5	GUA514		84.8	GUAL14		5.0	GUAW16		13.3
EAJC16		18.5	GUA59		77.8	GUAL16		13.3	GUAW24		5.8
EAJC26		20.5	GUAB14		5.0	GUAL24		5.8	GUAW26		13.5
EAJC36		20.5	GUAB16		13.3	GUAL26		13.5	GUAX14		5.0
EAJD16		18.5	GUAB24	1.6	5.8	GUAL36		15.5	GUAX16		13.3
EAJD26		20.5	GUAB26	1.6	13.5	GUAL47		27.5	GUAX24	0.8	5.8
EAJD36		20.5	GUAB36	1.7	15.5	GUAL49		76.0	GUAX26	1.3	13.5
EAJL16		18.5	GUAB47	1.8	27.5	GUAL59		77.8	GUAX36	1.1	15.5
EAJL26		20.5	GUAB59	2.0	80.0	GUAL69	4.0	80.0	GUAX37	1.5	27.5
EAJL36		20.5	GUAB69	2.0	80.0	GUAM14		5.0	GUAX47	1.3	27.5
EAJT16		18.5	GUAC14		5.0	GUAM16		13.3	GUAX49	2.0	80.0
EAJT26		20.5	GUAC16		13.3	GUAM24		5.8	GUAX59	1.9	77.8
EAJT36		20.5	GUAC24		5.8	GUAM26		13.5	GUAX69	1.7	80.0
EAJT49		80.0	GUAC26		13.5	GUAM47		27.5	GUE		55.0
EAJT59		80.0	GUAC36		15.5	GUAM69		80.0	GUP214		29.0
EAJT69		80.0	GUAC47		27.5	GUAN14		5.0	GUP215		29.0
EAJX16		18.5	GUAC49		80.0	GUAN16		13.3	GUR1		12.5
EAJX26		20.5	GUAC59		80.0	GUAN24	1.3	5.8	GUR2		12.5
EAJX36		20.5	GUAC69		80.0	GUAN26	2.3	13.5	GUR3		12.5



Powering Business Worldwide

# Bend radius and cubic capacity chart

## Form fittings

Cat. #	Bend radius (in.)	Internal volume (cu. in.)	Cat. #	Bend radius (in.)	Internal volume (cu. in.)	Cat. #	Bend radius (in.)	Internal volume (cu. in.)	Cat. #	Bend radius (in.)	Internal volume (cu. in.)
C1089	6.7	415.0	LB777	3.7	94.0	LR107	4.5	240.0	T107	4.0	217.4
C17	3.0	4.0	LB78	5.1	198.0	LR1089	6.7	415.0	T1089	6.7	415.0
C18	3.0	5.0	LB789	4.3	195.0	LR17	1.3	4.0	T17	1.2	5.8
C19	3.0	5.0	LB87	3.9	128.0	LR18	1.3	5.0	T18	1.0	6.0
C27	3.0	6.5	LB888	5.5	212.0	LR19	1.5	5.0	T19	1.4	4.0
C28	3.0	8.0	LB889	4.3	212.0	LR27	1.4	6.5	T27	1.3	9.0
C29	1.3	8.0	LB97	4.3	216.0	LR28	1.4	8.0	T28	1.1	10.0
C37	3.0	10.5	LB98	6.6	398.0	LR29	1.6	8.0	T29	1.6	8.0
C38	3.0	13.0	LB989	5.1	398.0	LR37	1.8	10.5	T37	1.4	14.5
C39	1.4	12.0	LBH10	1.0	8.3	LR38	1.6	13.0	T38	1.3	15.0
C448	3.0	24.0	LBH20	1.0	8.3	LR39	1.6	12.0	T39	1.9	12.0
C47	3.0	18.5	LBH30	1.3	32.8	LR448	2.1	24.0	T448	1.8	25.0
C49	1.5	25.0	LBH40	3.0	32.8	LR47	2.1	18.5	T47	1.6	18.5
C57	3.0	26.0	LBH50	4.0	80.3	LR49	2.2	25.0	T49	2.2	23.3
C58	3.9	42.5	LBH60	4.3	87.3	LR57	2.4	26.0	T57	1.9	26.0
C59	1.9	35.0	LBH80	7.0	212.0	LR58	3.1	42.5	T58	2.4	44.0
C67	3.0	46.0	LBH90	10.0	453.0	LR59	2.3	35.0	T59	2.6	31.5
C68	4.4	88.0	LBH100	10.0	507.0	LR67	2.8	46.0	T67	2.2	46.0
C69	2.1	75.0	LBY15	1.4	1.6	LR68	4.1	88.0	T68	2.9	88.0
C77	3.7	94.0	LBY25	2.2	2.7	LR69	3.0	75.0	T69	3.5	73.5
C78	5.1	198.0	LBY35	3.5	3.1	LR777	3.7	94.0	T77	3.2	94.0
C789	4.3	195.0	LBY45	6.0	6.4	LR78	5.4	195.0	T78	4.3	198.0
C87	3.9	128.0	LBY55	9.5	12.0	LR789	5.4	195.0	T789	5.2	195.0
C88	5.5	212.0	LL107	4.5	240.0	LR87	3.8	128.0	T87	3.4	128.0
C889	4.3	212.0	LL1089	4.3	415.0	LR888	5.5	212.0	T88	4.3	212.0
C989	4.3	212.0	LL17	1.3	4.0	LR889	5.4	212.0	T889	5.4	212.0
LB107	5.6	240.0	LL18	1.3	5.0	LR97	4.4	216.0	T97	4.3	216.0
LB108	6.6	415.0	LL19	1.5	5.0	LR989	6.5	385.5	T989	6.5	398.0
LB1089	5.3	415.0	LL27	1.4	6.5	OEC1		5.0	TB17	1.5	5.8
LB17	1.5	4.0	LL28	1.4	8.0	OEC2		8.3	TB18	1.6	6.0
LB18	1.6	5.0	LL29	1.6	8.0	OEC3		16.5	TB19	1.0	4.0
LB19	1.0	5.0	LL37	1.8	10.5	OELB1		5.0	TB27	1.8	9.0
LB27	1.8	6.5	LL38	1.6	13.0	OELB2		8.0	TB28	2.1	10.0
LB28	2.1	8.0	LL39	1.6	12.0	OELB3		16.0	TB29	1.3	8.0
LB29	1.3	8.0	LL448	2.1	24.0	OELL1		5.0	TB37	2.0	14.5
LB37	2.0	10.5	LL47	2.1	18.5	OELL2		8.5	TB38	2.5	15.0
LB38	2.5	13.0	LL49	2.2	25.0	OELL3		16.5	TB39	1.4	12.0
LB39	1.4	12.0	LL57	2.4	26.0	OELR1		5.0	TB47	2.3	18.5
LB448	2.8	24.0	LL58	3.1	42.5	OELR2		8.3	TB448	2.3	25.0
LB47	2.3	18.5	LL59	2.3	35.0	OELR3		13.8	TB49	1.5	23.3
LB49	1.5	25.0	LL67	2.8	46.0	OET1		4.8	TB57	2.5	26.0
LB57	2.5	26.0	LL68	4.1	88.0	OET2		8.3	TB58	3.9	44.0
LB58	3.9	42.5	LL69	3.0	75.0	OET3		16.0	TB59	1.9	31.5
LB59	1.9	35.0	LL777	3.7	94.0				TB67	2.9	46.0
LB67	2.9	46.0	LL78	5.4	195.0				TB68	4.4	88.0
LB68	4.4	88.0	LL789	4.3	195.0				TB69	2.1	73.5
LB69	2.1	75.0	LL87	3.8	128.0						
			LL888	5.5	212.0						
			LL889	4.3	212.0						
			LL97	4.4	216.0						

## Moguls

Cat. #	Bend radius (in.)	Internal volume (cu. in.)	Cat. #	Bend radius (in.)	Internal volume (cu. in.)	Cat. #	Bend radius (in.)	Internal volume (cu. in.)	Cat. #	Bend radius (in.)	Internal volume (cu. in.)
BC3	3.0	19.0	BLB7	3.9	162.0	BUB4	6.0	25.0	LBD3300	2.3	9.0
BC4	3.0	25.0	BLB8	4.6	201.0	BUB5	9.3	57.0	LBD4400	3.0	28.3
BC5	4.4	57.0	BLB9	4.6	374.0	BUB6	9.4	75.0	LBD5500	4.0	82.0
BC6	4.4	75.0	BT10	4.6	426.0	BUBXL6	8.8	80.0	LBD6600	4.3	84.0
BC7	5.3	162.0	BT3	2.0	19.0	BUB7	12.4	147.0	LBD7700	7.0	205.0
BC8	5.3	201.0	BT4	2.0	25.0	BUB8	12.8	217.0	LBD8800	7.0	212.0
BC9	5.3	374.0	BT5	3.0	57.0	BUBXL8	14.8	259.0	LBD9900	10.0	453.0
BC10	5.3	426.0	BT6	2.7	75.0	BUB9	16.6	348.0	LBNEC10	10.0	776.7
BLB10	4.6	418.0	BT7	4.3	163.0	LBD012	17.0	1471.5	LBNEC7	7.0	398.0
BLB3	1.9	19.0	BT8	3.9	211.0	LBD014	20.0	2322.0	LBNEC8	7.0	398.0
BLB4	2.4	25.0	BT9	4.6	375.0	LBD10900	10.0	507.0	LBNEC9	10.0	776.7
BLB5	2.5	57.0	BUB10	16.8	397.0	LBD1100	1.3	3.3			
BLB6	3.1	75.0	BUB3	5.8	19.0	LBD2200	2.0	6.5			

**Eaton**  
1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
Eaton.com

**Eaton's Crouse-Hinds Division**  
1201 Wolf Street  
Syracuse, NY 13208  
Crouse-Hinds.com

© 2018 Eaton  
All Rights Reserved  
Printed in USA  
April 2018

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Powering Business Worldwide