



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street  
75964-7263, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## F96T12CWH0COLD 110W T12 96" Cool White Cold Temp Ho 60 Cri R17D

*Sylvania-Ledvance*

Catalog Number	F96T12CWH0COLD
Manufacturer	Sylvania-Ledvance
Description	Linear Fluorescent Lamp, Recessed Double Contact Base, T12 Bulb Shape, 60, 12000 H Average Life, 4200 K, Cool White, 800 Ma, 110 W, 8600 LM Brightness (Lumens), Phosphor Coated, C78.81 – 2001 Ansi Ballast Code, 1.593 In Diameter, 96.0 In Length, Rapid, 1.41 LB/Ea
Weight per unit	1.4 (lbs/each)
Product Category	Linear Fluorescent Straight La

### Features

Base	Recessed Double Contact
lumens	8.6k lm
Shape	T12
total harmonic distortion	Ballast Dependent
Wattage	110 WTT

### Material, Color, and Finish

color rendering index (cri)	60 WTT
-----------------------------	--------

### Descriptions

Description	110W T12 96" COOL WHITE COLD TEMP HO 60 CRI R17D
Special Features	COOL WHITE

### Manufacturer Information

Brand	Sylvania (Usc)
GTIN	00046135251344
Manufacturers Part Number	F96T12/CW/HO/COLD-TEMP/25134
UPC	046135251344

### Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT

### Packaging

Carton	1
Package	15
Weight Per each	1.41

### Uses, Certifications, and Standards

Application	COMMERCIAL/RESIDENTIAL
-------------	------------------------

**Product Number:** 25134

**Order Abbreviation:** F96T12/CW/HO/COLD TEMP

**General Description:** 110W, 96" MOL, T12 HO (800 mA) rapid start fluorescent lamp, Cool White phosphor, 4200K color temperature, 60 CRI, labeled for cold temperature operation (below 60 degrees F) per EPACT. 12000 Avg rated life at 3 hrs/start



**\* Full Case Required**

#### Product Information

Abbrev. With Packaging Info.	F96T12CWHOCOLDTEMP 15/CS 1/SKU
Actual Length (in)	93.909
Actual Length (mm)	2385.29
Average Rated Life (hr)	12000
Base	Recessed Double Contact
Bulb	T12
Color Rendering Index (CRI)	60
Color Temperature/CCT (K)	4200
Diameter (in)	1.593
Diameter (mm)	40.46
Initial Lumens at 25C	8600
Mean Lumens at 35C	6966
Nominal Length (in)	96.000
Nominal Length (mm)	2438.40
Nominal Wattage (W)	110.00

#### Footnotes

- Approximate initial lumens after 100 hours operation.
- The life ratings of fluorescent lamps are based on 3 hr. operating cycles under specified conditions and with ballast meeting ANSI specifications. If operating cycle is increased, there will be a corresponding increase in the average hours life.
- Minimum starting temperature is a function of the ballast; consult the ballast manufacturer.
- Labeled for cold temperature (below 60 degrees F) operation only per EPACT.\*
- Average life rating at 12 hours operation per start is 18,000 hours.