ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



# FB031835 31W T8 22.5" 1 5/8" Leg Spacing 3500K 82 Cri

*Sylvania-Ledvance*

| | |
|---|---|
| Catalog Number | FB031835 |
| Manufacturer | Sylvania-Ledvance |
| Description | 31W, 22.5" Mol, T8 Octron Curvalume Fluorescent Lamp, 1 5/8" Leg Spacing, 3500K Color Temperature Rare Earth Phosphor, 82 Cri, Suitable For Is or RS Operation |
| Weight per unit | 0.7000 (lbs/each) |
| Product Category | Shape Lamps |

## Features

| | |
|---|---|
| amperage rating | Ballast Dependent |
| average life | 20000 |
| Base | Medium Bipin |
| bulb type | T8 |
| Lamp Type | RS-CURVALUME |
| Shape | T8 |
| total harmonic distortion | Ballast Dependent |
| Voltage Rating | Ballast Dependent |
| Wattage | 31 |

## Material, Color, and Finish

| | |
|---|---|
| color rendering index (cri) | 82 |
| color temperature | 3500 |
| Finish | Phosphor Coated |

## Dimensions and Weight

| | |
|---|---|
| Diameter | 1 |

## Descriptions

| | |
|---|---|
| Description | 31W T8 22.5" 1 5/8" LEG SPACING 3500K 82 CRI |
| extra long description | LDV FBO31/835/21878 FBO31835 15/CS |
| Long Description | 31W, 22.5" MOL, T8 OCTRON Curvalume fluorescent lamp, 1 5/8" leg spacing, 3500K color temperature rare earth phosphor, 82 CRI, suitable for IS or RS operation |
| Product Type | FBO31835 15/CS 1/Sku |

## Manufacturer Information

| | |
|---|---|
| Brand | SYLVANIA |
| GTIN | 00046135218781 |
| Manufacturers Part Number | FBO31/835/21878 |
| UPC | 046135218781 |

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

| | |
|---|---|
| Category Description | Fluorescent |
| Type | FLUORESCENT |

## Packaging

| | |
|---|---|
| Carton | 1 |
| Package | 15 |
| Weight Per each | 0.7 |

## Uses, Certifications, and Standards

| | |
|---|---|
| Application | Commercial/Residential |