Elliott Electric Supply

We Deliver...Lower Cost, Quality Products, & Personal Service

1105 West Sanger
88240-0000, NM Hobbs
Phone: 575-397-2122
Fax: 575-397-2178



HBL2430 Locking Recp 20A 3P 480V L16-20R BK

Hubbell Incorporated Delaware

Catalog Number	HBL2430
Manufacturer	Hubbell Incorporated Delaware
Description	Locking Devices, Twist-Lock®, Industrial, Single Flush Receptacle, 20A 3-Phase 480V Ac, 3-Pole 4-Wire Grounding, Nema L16-20R, Screw Terminal, Nylon Face, Back and Side Wire, Black.
Weight per unit	0.2500 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	20
connection	Screw Terminal
Current Rating	20
Dielectric Strength	Withstands 2,000V minimum
Material	Nylon
Number of Wires	4-Wire
pallet quantity	3240
Phase	3
Poles	3-Pole
Voltage Rating	3 Phase 480 VAC
Wattage	9,600
Wire Size	#16 to #8

Dimensions and Weight

Size	3.28 in x 1.7 in x 1.23 in

Descriptions

Description	LOCKING RECP 20A 3P 480V L16-20R BK
extra long description	HWDK HBL2430 LKG RCPT, 20A 3P 480V,
Long Description	Locking Devices, Twist-Lock®, Industrial, Single Flush Receptacle, 20A 3-Phase 480V AC, 3-Pole 4-Wire Grounding, NEMA L16-20R, Screw Terminal, Nylon face, Back and side wire, Black.
Product Type	LKG RCPT, 20A 3P 480V, L16-20R, BK
Special Features	Standard

Manufacturer Information

Brand	Hubbell Wiring Device-Kellems
GTIN	00783585235776
Manufacturers Part Number	HBL2430
UPC	783585235776

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
1105 West Sanger
88240-0000, NM Hobbs
Phone: 575-397-2122
Fax: 575-397-2178

Taxonomies, Classifications, and Categories

Category Description	Industrial receptacles
Type	Single Flush Receptacle

Packaging

Carton	1
Package	10
Weight Per each	0.25

Uses, Certifications, and Standards

Application	Heavy Duty Industrial
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
nema rating	L16-20R
standard	Certified to CSA C22.2 No.42;Fed.Spec. W-C-596;Listed to UL 498;WR Rating