ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
5018 W Main Street
74701-0000, OK Durant
Phone: 580-745-5448
Fax: 580-745-5449



FD3020L Type FD BRKR 3P 20A 600VAC Max 18K Aic

Eaton Corp

Catalog Number	FD3020L
Manufacturer	Eaton Corp
Description	Eaton Series C Complete Molded Case Circuit Breaker, F-Frame, FD, Complete Breaker, Fixed Thermal, Fixed Magnetic Trip Type, Three-Pole, 20A, 600 Vac, 250 VDC, 65 Kaic At 240 Vac, 35 Kaic At 480 Vac, Line and Load, 50/60 HZ
Weight per unit	4.5 (lbs/each)
Product Category	3 Pole

Features

Current Rating	20 A
dimensions	3.3800 IN X 4.1300 IN X 6.0000 IN
frame	F
interrupt rating	35 kAIC at 480 Vac65 kAIC at 240 Vac
Poles	Three-pole
Trip Type	T186
Voltage Rating	600 VAC, 250 VDC

Descriptions

Description	TYPE FD BRKR 3P 20A 600VAC MAX 18K AIC
extra long description	ETN FD3020L TYPE FD BRK 3P 20A 600V
Features	Experience the superior quality of the Eaton Series C Molded Case Circuit Breaker. The Series C circuit breaker is ideal for panelboards, switchboards, motor control centers, and busway applications. Choose from a premier selection of trip units including thermal magnetic, electronic, and magnetic only switches. Available for systems up to 600 VAC or 250 VDC with current ratings up to 800A.
Long Description	Eaton Series C complete molded case circuit breaker, F-frame, FD, Complete breaker, Fixed thermal, fixed magnetic trip type, Three-pole, 20A, 600 Vac, 250 Vdc, 65 kAIC at 240 Vac, 35 kAIC at 480 Vac, Line and load, 50/60 Hz
Product Type	Type FD BRK 3P 20A 600VAC Max 18K Aic

Manufacturer Information

Brand	Eaton
GTIN	00786679305638
Manufacturers Part Number	FD3020L
UPC	786679305638

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
5018 W Main Street
74701-0000, OK Durant
Phone: 580-745-5448
Fax: 580-745-5449

Taxonomies, Classifications, and Categories

Category Description	MOLDED CASE BREAKERS
Type	Molded case circuit breaker

Packaging

Carton	1
Weight Per each	4.5

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & EOEM - Electrical Assemblies and EOEMs - Other
Frequency Rating	50/60 Hz
standard	UL Listed