



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HBL5379C FLG-RCPT, 20A 125V, 5-20P, SS *Hubbell Wiring Devices*

Catalog Number	HBL5379C
Manufacturer	Hubbell Wiring Devices
Description	Straight Blade Devices, Inlets, Flanged, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R, Stainless, Single Pack.
Weight per unit	0.1500 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	20
connection	Back and Side Wired Screw Terminals
Current Rating	20
Dielectric Strength	Withstands 2,000V minimum
Number of Wires	3-Wire
Phase	1
Poles	2-Pole
Voltage Rating	125 VAC
Wattage	2,500
Wire Size	#18 to #12

Dimensions and Weight

Size	1.71 in x 1.69 in x 1.71 in
------	-----------------------------

Descriptions

Description	FLG-RCPT, 20A 125V, 5-20P, SS
extra long description	HWDK HBL5379C FLG-RCPT, 20A 125V, 5
Long Description	Straight Blade Devices, Inlets, Flanged, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R, Stainless, Single Pack.
Product Type	FLG-RCPT, 20A 125V, 5-20P, SS
Special Features	Impact resistant thermoplastic construction

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585174457
Manufacturers Part Number	HBL5379C
series	Extra Heavy Duty
UPC	783585174457

Taxonomies, Classifications, and Categories

Category Description	Industrial receptacles
Type	Flanged Receptacle



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	10
Weight Per each	0.15

Uses, Certifications, and Standards

Application	Heavy Duty
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
nema rating	5-20R
standard	Certified to CSA, C22.2, No. 42;NEMA® WD-6 Compliant;UL Listed, File E2186