# Metalux

## DESCRIPTION

The HBL series is ideal for high mounting height industrial or retail applications. Advanced optical designs provide maximum performance from either T5 or T8 lamps. Optional uplight component produces excellent ceiling uniformity. HBL's high lumen package allows the benefits of fluorescent to be applied at high mounting heights that were traditionally exclusive to H.I.D. Benefits include exceptional color rendering, high system efficacy, 95% lumen maintenance, long lamp life, instant on/instant re-strike, economical dimming, and uniform brightness control. Typical HBL applications include retail, shopping malls, light industrial and recreational environments.

## SPECIFICATION FEATURES

#### Construction

Channel and end plates are constructed of die formed steel. The channel provides strength, numerous KOs for easy installation, and excellent thermal dissipation without any special or proprietary components. Stiffening brackets add additional strength and rigidity to channel and reflectors.

#### Electrical

The HBL comes with a standard Class "P" electronic ballast and twist-lock lampholders. UL/ cUL listed for high ambient environments up to 55°C (131°F) for all lamp and ballast combinations listed. Suitable for damp locations.

#### Finish

Electrostatically applied baked white enamel finish is preceded by a multistage cleaning cycle, iron phosphate coating with rust inhibitor.

#### Optics

Die formed, segmented optical design optimizes performance across three distributions. Optical choices include a narrow distribution for aisles, medium distribution for assembly and loading areas, or wide distribution for general, open area lighting. An uplight option is offered to permit ceiling uniformity and allow for ample lamp and luminaire heat dissipation.


Catalog #	Туре
Gutulog #	
Project	
Comments	Date
Prepared by	

#### Warrantv


When operated in high ambient conditions, the HBL is supported by a 5 yr/55°C and 3 yr/65°C ballast warranty for T5 and T8 (277V) options when used w/ high temperature ballast in open, uplight configurations. To maximize your warranty, the HBL should be ordered with a hightemperature ballast in ambient environments that typically exceed 40°C (102°F).

#### Compliance


Options to meet Buy American and other domestic preference requirements.



## LAMP CONFIGURATIONS



## DIMENSION TOP VIEW





## HBL SERIES

## 4 OR 6 T8 LAMPS

High-Bay Industrial Open Luminaire





#### ENERGY DATA

Input Watts: **EB Ballast and STD Lamps** 432 = 109632=167

Luminaire Efficacy Rating LER = 88 (White) LER = 90 (Specular Inserts) Catalog Number: HBL-632-UPL

Yearly Cost of 1000 lumens, 3000 hrs at .08 KWH = \$2.67

\*Reference the lamp/ballast data in the Technical Section for specific lamp/ballast requirements

\*\*Consult Pre Sales Technical Support.







Across ⊥

4685

4692

4654

4594

4503

4374

4203

4000

3774

3562

3354

3150

2962

2707

2246


1685

1107

566

177

## PHOTOMETRICS



## Candela

Across 1

6445

6322

5913

5455

5075

4736

4478

4363

4043

3636

3321

2987

2737

2614

2148

1622

1094

592

182

Narrow Distribution			
(2) Electronic Plus	Angle	Along II	45°
Ballasts	0	6445	6445
(6) F32/T8/TL835 32W	5	6418	6359
(-)	10	6339	6092
T8 lamps, 3100 lumens	15	6200	5715
Spacing criterion:	20	6008	5300
(II) 1.3 x mounting	25	5761	4910
height, $(\perp)$ 1.0 x	30	5464	4549
	35	5119	4178
mounting height	40	4731	3898
Efficiency 95.9%	45	4302	3674
,	50	3840	3287
Test Report:	55	3346	2841
HBL632NUPL.IES	60	2827	2482
LER =90	65	2286	2118
	70	1732	1892
Yearly Cost of 1000	75	1179	1543
lumens, 3000 hrs at	80	654	1018
.08 KWH = \$2.67	85	201	522
φ2.07	90	3	117

LER =90 Yearly Co lumens, 3 .08 KWH

HBL-632-N-UPL


#### **Coefficients of Utilization**

	Eff	ectiv	e flo	oor ca	wity re	flect	tance	e	20%									
rc		80	%			70	%		5	50%			30%			10%		0%
rw	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	110	110	110	110	104	104	104	99	99	99	94	94	94	92
1	103	98	93	89	100	95	91	88	90	87	84	86	83	81	82	80	78	75
2	93	85	78	72	90	82	76	71	78	73	69	75	70	66	71	68	64	62
3	85	74	66	60	82	72	65	59	69	62	57	66	60	56	63	58	54	52
4	77	66	57	50	75	64	56	50	61	54	49	58	52	47	56	51	46	44
5	71	58	50	43	69	57	49	43	55	47	42	52	46	41	50	45	40	38
6	66	53	44	38	64	52	43	37	49	42	37	47	41	36	45	40	35	33
7	61	48	39	33	59	47	39	33	45	38	33	43	37	32	42	36	31	29
8	57	44	35	30	55	43	35	30	41	34	29	40	33	29	38	33	28	26
9	53	40	32	27	51	39	32	27	38	31	26	37	30	26	35	30	26	24
10	50	37	29	24	48	36	29	24	35	28	24	34	28	24	33	27	23	22

#### Zonal Lumen Summary

Luminance Data

Zone	Lumens	%Lamp	%Fixture	Angle in Deg	Average 0-Deg cd/sm	Average 45-Deg cd/sm	Average 90-Deg cd/sm
0-30	4562	24.5	25.6				
0-40	7330	39.4	41.1	45	10283	8782	8691
0-60	12827	69.0	71.9	55	9860	8372	8802
	-			65	9142	8470	10454
0-90	17094	91.9	95.8	75	7699	10076	10592
0-180	17837	95.9	100.0				
				85	3808	10123	11/180



UPL			
Wide Distribution	Angle	Along II	45°
(2) Electronic Plus	0	4685	4685
Ballasts	5	4663	4674
	10	4608	4631
(6) F32T8/835 32WT8	15	4512	4555
lamps, 3100 lumens	20	4380	4446
Spacing criterion:	25	4209	4303
(II) 1.3 x mounting	30	4000	4121
	35	3762	3909
height, (⊥) 1.3 x	40	3492	3658
mounting height	45	3195	3377
Efficiency 90.5%	50	2870	3081
,	55	2527	2785
Test Report:	60	2165	2500
HBL632WUPL.IES	65	1781	2230
LER =88	70	1384	1985
LEN =00	75	975	1569
Yearly Cost of 1000	80	569	1025
lumens, 3000 hrs at	85	200	500
.08 KWH = \$2.73	90	3	111

#### **Coefficients of Utilization**

С		80	%			70	%			50%			30%			10%		0%
	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
	106	106	106	106	103	103	103	103	97	97	97	91	91	91	86	86	86	83
	96	91	87	83	93	88	84	81	83	80	77	78	76	73	74	72	70	68
	86	78	72	66	83	76	70	65	72	67	62	68	63	60	64	60	57	55
	78	68	60	54	75	66	59	53	62	56	51	59	54	50	56	52	48	46
	71	60	52	45	69	58	51	45	55	49	43	52	47	42	49	45	41	38
	65	53	45	39	63	52	44	38	49	42	37	47	41	36	44	39	35	33
	60	48	40	34	58	47	39	33	44	37	32	42	36	31	40	35	31	28
	56	43	35	29	54	42	34	29	40	33	28	38	32	28	36	31	27	25
	52	39	31	26	50	38	31	26	37	30	25	35	29	25	33	28	24	22
)	48	36	28	23	47	35	28	23	34	27	23	32	26	22	31	25	22	20
)	45	33	26	21	44	32	26	21	31	25	20	30	24	20	28	23	20	18


#### Zonal Lumen Summary

Zone	Lumens	%Lamp	%Fixture	Angle	Average 0-Deg	Average 45-Deg	Average 90-Deg
0-30	3714	20.0	22.1	in Deg	cd/sm	cd/sm	cd/sm
0-40	6154	33.1	36.6	45	7432	7855	8286
0-60	11290	60.7	67.1	55	7247	7987	9033
	15508	83.4	92.1	65	6932	8679	10536
0-90				75	6196	9971	10708
0-180	16834	90.5	100.0	85	3774	9436	10682

Luminance Data

## Modular F-Bay Power Supply Option

Cooper Lighting's F-Bay Modular Power Supply option is available for use with all F-Bay products. The modular power supply allows external fixture access for safe and easy servicing. There is no need to remove lamps or reflectors to disconnect fixture power with F-Bay Modular Power Supply. Access to the individual fixture's power supply allows servicing without turning off all the fixtures, disrupting occupants. F-Bay Modular Power Supply is a time-saver in installation - simply plug & power.



- 1. Modular Power Supply Receptacle supplied mounted into fixture Access Plate
- 2. Modular Power Cord & Plugs in 120, 277, 347, & 480V configurations for easy plug & power into existing supply



No internal fixture access required for installation or disconnecting power



Modular Motion Sensor Option supplied with Mounting Box and Modular Power Supply Receptacle

#### **Code Compliance**

- UL/cUL Certified for Make/Break under load (UL2549)
- Meets NEC requirements for ballast disconnect (NEC 410.73G)
- Allows for addition of Occupancy Sensor without hard connections
- · Receptacles complete with insulating/dust cap



Cooper Lighting Solutions 1121 Highway 74 South Peachtree City, GA 30269 P. 770-486-4800 www.cooperlighting.com

© 2023 Cooper Lighting Solutions All Rights Reserved.

Specifications and dimensions subject to change without notice.

#### ORDERING INFORMATION

Domestic Preferences (*) [Blank]=Standard BAA=Buy American Act TAA=Trade Agreements Act Width Blank=20" wide 4 & 6 Lamp (nominal) Series HBL=Linear High Bay No. of Lamps 6=6 Lamps 6=6 Lamps Lamp Type	Voltage <sup>(1)</sup> UNV=Universal 120/277 Voltage UNC=Universal 347/480 Voltage <sup>(7)</sup> 120V=120 Volt 277V=277 Volt 347V=347 Volt Options GL=Single Element Fuse GM=Double Element Fuse EL=Emergency Installed	Ballast Type <sup>(4)</sup> T8 Systems   EB8 _=T8 Electronic Instant Start.   Total Harmonic Distortion < 10%	Options     UPL=Uplight Apertures on Reflector     MP=Modular Power Receptacle     (Used for all Cord or Cord and Plug options) <sup>(2), (8)</sup> MWS=Modular Wiring System <sup>(3)</sup> MS=360° or 180° Motion Sensor installed (120V through 347V, or 48     Accessories (order separately) <sup>(10)</sup> HBL-SPM=Single Monopoint Hang; FH-1=Fixture Hook     FL-1=Fixture Loop     Y-TOGGLE2PK=(2) Y-Toggle Call (Specify 10 or 30 for length in feet)     HBAYC-CHAIN/SET/U=(2) V-Hook H Sets w/S-Hooks     MC3=3' Modular Power Cord     MPC3=3' Modular Power Cord     MPC3=6' Modular Power Cord	er w/Hub ble Kits Hanger, 36" Chai lug (Specify
32=32WT8 Lamp (48" Long) Distribution N=Narrow Beam (Standard) M=Medium Beam W=Wide Beam			MPC6=6' Modular Power Cord & Pl Voltage) MMS=360° or 180° Aisle Motion Se Power Receptacle (120-277V) <sup>(2)</sup> MDS6=6' Modular Power Cord with 27DS18/2G06MP Connector <sup>(8)</sup> WG/HBL6-4FT-B=4/6 Lamp Wiregu:	ensor with Modu

Specifications & dimensions subject to change without notice. Consult your Cooper Lighting Solutions Representative for availability and ordering information.

## QUICK SHIP ORDERING INFORMATION



Quick Ship Ordering Information Sample Number: HBL432-MP-UPL-L5 Includes V Hangers for rapid installation<sup>(6)</sup> Quick Ship orders ship in 5 days in order quantities not to exceed 200 pieces.

NOTE: Orders received after noon are entered on the following day.

Family HBL	Lamp Type 32=32W T8 Lamps (48")	Ballast Type T8 Systems <sup>(4)</sup> Blank=(1) or (2) 120/277V T8 Instant	Power Receptacle MP=Modular Power Receptacle <sup>(8)</sup>	Uplight Blank=No Uplight UPL=Uplight
<b>No. of Lamps</b> <b>4</b> =4 Lamps <b>6</b> =6 Lamps	Distribution Blank=Narrow Beam W=Wide Beam	Start Electronic, 1.15 BF <b>PS</b> =(1) or (2) 120/277VT8 Electronic Program Rapid Start, 1.15 BF <sup>(7)</sup>		

NOTES: <sup>(7)</sup>Recommended when using motion sensor options. <sup>(8)</sup>Requires use of Modular cord and plug accessories.

## SHIPPING DATA

Catalog No.	
HBL-432-UNV-UPL	
HBL-632-UNV-UPL	

Wt. 13.5 lbs. 15 lbs.



**Cooper Lighting Solutions** 1121 Highway 74 South Peachtree City, GA 30269 P: 770-486-4800 www.cooperlighting.com

© 2023 Cooper Lighting Solutions All Rights Reserved.

Specifications and dimensions subject to change without notice.

ADF081930 February 20, 2023 7:29 AM