
# HBLED13A



## **Technical Specifications**

### Compliance

### **UL Listed:**

Suitable for wet locations. Suitable for ground mounting.

#### IESNA LM-79 & IESNA LM-80 Testing:

RAB LED luminaires and LED components have been tested by an independent laboratory in accordance with IESNA LM-79 and LM-80.

#### **DLC Listed:**

This product is listed by Design Lights Consortium (DLC) as an ultra-efficient premium product that qualifies for the highest tier of rebates from DLC Member Utilities. Designed to meet DLC 5.1 requirements. DLC Product Code: PV5TSVJA

### Performance

#### Lifespan:

100,000-Hour LED lifespan based on IES LM-80 results and TM-21 calculations

### Construction

### Swivels:

Fully adjustable with sure-grip locks. 1/2" NPS threaded arm with serrated locking swivel fits all standard mounting covers. Color matched EZ Grip lock nuts. Stainless steel screw.

#### Housing:

Precision die-cast aluminum housing

Gaskets:

High-temperature Silicone

## Finish:

Formulated for high durability and long-lasting color

### Green Technology:

Mercury and UV free. RoHS-compliant components.

#### **Cold Weather Starting:**

Minimum starting temperature is -40°C (-40°F)

#### Maximum Ambient Temperature:

Suitable for use in up to 40°C (104°F)

### LFLOOD 13W:

LED Floodlight that reduces energy consumption by 85% compared to 100W PAR38. Spot and Flood beam patterns. Recommended for Residential and Commercial applications.

Type:

Date:

13W

1,980

5000K (Cool)

100,000 Hours

146.7 lm/W

### Other

#### Warranty:

RAB warrants that our LED products will be free from defects in materials and workmanship for a period of five (5) years from the date of delivery to the end user, including coverage of light output, color stability, driver performance and fixture finish. RAB's warranty is subject to all terms and conditions found at rablighting.com/warranty.

#### **Equivalency:**

250W BR40

### **Technical Specifications (continued)**

### Other

### Patents:

LFLOOD thermal Management technology is protected under utility patents pending in the U.S., Canada and China.

### Buy American Act Compliance:

RAB values USA manufacturing! Upon request, RAB may be able to manufacture this product to be compliant with the Buy American Act (BAA). Please contact customer service to request a quote for the product to be made BAA compliant.

### **LED Characteristics**

### Lumen Maintenance:

The LED will deliver 70% of its initial lumens at 100,000 hours of operation

### **Color Consistency:**

**Ordering Matrix** 

7-step MacAdam Ellipse binning to achieve consistent fixture-to-fixture color

### Color Stability:

LED color temperature is warrantied to shift no more than 200K in color temperature over a 5-year period

### Color Uniformity:

RAB's range of Correlated Color Temperature follows the guidelines of the American National Standard for Specifications for the Chromaticity of Solid State Lighting (SSL) Products, ANSI C78.377-2017.

### Optical

### **Reflectors:**

NEMA 5x5 floodlight reflector. Photometrics show flood configuration.

### Electrical

### Driver:

Constant Current, 120-277V with 4kV surge protection, 120V: 0.12A, 208V: 0.07A, 240V: 0.06A, 277V: 0.06A

### THD:

4kV

10.08% at 120V, 10.94% at 277V

### **Power Factor:**

99% at 120V, 91.7% at 277V

### Surge Protection:

Dimensions

### Features

80% energy savings vs. PAR floods Mount on junction box or on RAB Mighty Post Patent-pending "Air-Flow" technology 5-Year, No-Compromise Warranty

#### Family Wattage Color Temp Finish **Driver Options** HBLED 13 А 18 = 18W Blank = 5000K (Cool) A = Bronze Blank = No Option 26 = 26W **N** = 4000K (Neutral) W = White /D10 = 0-10V Dimming **Y** = 3000K (Warm) **B** = Black /480 = 480V (Only available for 26W) VG = Verde Green