Project	Catalog #	Тур	ре
Prepared by	Notes	Dat	ite



HC6 | HM6 | 61 | 61PS

HALO Commercial

6-inch LED new construction/remodel regressed lens downlight and wall wash

Typical Applications

Office · Healthcare · Hospitality · Institutional · Mixed-Use/Retail

Product Certification







Product Features

Order Information page 2
Product Specifications page 4


Interactive Menu

- Photometric Data page 5
- Energy & Performance Data page 8
- Connected Systems page 9
- Product Warranty

Top Product Features

- New construction/remodel series; 1,000 to 4,000 lumens
- · Narrow, Medium and Wide distributions; Wall wash with rotatable linear spread lens
- 2700K, 3000K, 3500K and 4000K CCT; 80 or 90 CRI
- Universal voltage 120V-277V; Standard 0-10V driver dims to 1%
- · Two retrofit kits install from below ceiling for LED upgrades

Dimensional and Mounting Details







Order Information

Sample Number: HC620D010REM7 - HM612835 - 61MDC

A complete luminaire consists of a housing frame, LED module, and reflector (ordered separately)

Mounting Frame	Lumens	Input / Control	Factory Installed Options	Accessories
Mounting Frame	Lumens	Input / Control	Factory Installed Options	Accessories
HC6 = 6" new construction and remodeler housing HC6CP = 6" new construction and remodeler housing, CCEA Chicago Plenum rated	10 = 1000 lumens (nominal) 15 = 1500 lumens (nominal) 20 = 2000 lumens (nominal) 30 = 3000 lumens (nominal) 40 = 4000 lumens (nominal)	D010=120-277VAC 50/60Hz 0-10V analog 1% - 100% dimming D010347 = 347VAC 50/60Hz 0-10V analog 1%-100% dimming (Canada only) ¹ DLV = Distributed Low Voltage driver, 1%-100% dimming DLV for use with DLVP system only. Refer to DLVP low-voltage power module and DLVP specifications for details. ⁽¹⁾	REM7 = 7 watt emergency module with remote test / indicator light, use with D010 only ¹ REM14 = 14 watt emergency module with remote test / indicator light, use with D010 only ¹ IEM7 = integral 7 watt emergency module with integral test / indicator light, use with D010 only ¹ IEM14 = integral 14 watt emergency module with integral test / indicator light, use with D010 only ¹ B0D7ST = 7.5 watt Bodine self-test diagnostic emergency module with remote test / indicator light, use with D010 only ¹⁰ WTA = Factory installed WaveLinx tile mount sensor Kitt ⁽¹⁰⁾ WTK = Factory installed WaveLinx Lite Sensor Kitt ⁽¹⁰⁾ REMV7 = 7 watt emergency module with remote test / indicator light, use with DLV only ^{1,2} IEMV7 = integral 7 watt emergency module with integral test / indicator light, use with DLV only ^{1,2} IEMV74 = integral 14 watt emergency module with integral test / indicator light, use with DLV only ^{1,2} IEMV74 = integral 14 watt emergency module with integral	HB128APK = L channel hanger bar, 26", pair (replacement) RMB22 = Adjustable wood joist mounting bars, pair, extend to 22" long HSA6=Stope Adapter for 6" Aperture Housings, Specify Slope (refer to instructions for installation of housing and trim) H347 = 347 to 120V step down transformer, 75VA H347200 = 347 to 120V step down transformer, 200VA WTA=Field installed WaveLinx Lite Sensor Kit ¹¹⁵ WTK = Field installed WaveLinx Lite Sensor Kit ¹⁰⁰⁰
Notes	Notes	Notes	Notes	Notes
		(1) Not available with CP version	 Not available with CP version ULus for U.S. only WTA = WaveLinx tile mount sensor kit for daylight dimming, PIR motion sensing, and optional RLIS - Real Time Location Services, use with DOI only (Refer to WaveLinx system specifications) WTK = WaveLinx Lite tile mount sensor kit for daylight dimming, PIR motion sensing, use with DO10 only (Refer to WaveLinx Lite system specifications) 	(1) Not available with CP version (5) WTA = WaveLinx tile mount sensor kit for daylight dimming, PIR motion sensing, and optional RLTS - Real Time Location Services, use with D010 only (Refer to WaveLinx system specifications) (6) WTK = WaveLinx Lite tile mount sensor kit for daylight dimming, PIR motion sensing, use with D010 only (Refer to WaveLinx Lite system specifications)

LED Module	Lumens	CRI/CCT	
LED Module	Lumens	CRI/CCT	
HM6 = 6" LED module	12=1000, 1500 and 2000 lumens (nominal), use with HC610*, HC615*, HC620* housings 34=3000 and 4000 lumens (nominal), use with HC630*, HC640* housings	827 = 80 CRI (minimum), 2700K CCT 927 = 90 CRI (minimum), 2700K CCT 830 = 80 CRI (minimum), 3000K CCT 930 = 90 CRI (minimum), 3000K CCT 835 = 80 CRI (minimum), 3500K CCT 935 = 90 CRI (minimum), 3500K CCT 840 = 80 CRI (minimum), 4000K CCT 940 = 90 CRI (minimum), 4000K CCT	
Notes	Notes	Notes	

Reflector	Distribution	Finish	Flange	Accessories
Reflector	Distribution ³	Finish	Flange	Accessories
61 = 6" conical reflector	ND = narrow 55° beam angle 0.97 SC MD = medium 60° beam angle 1.10 SC WD = wide 65° beam angle 1.28 SC RWW = rotatable wall wash with linear spread lens	C = Specular clear H = Semi-specular clear W = White	Blank = Polished flange standard with C & H reflectors Blank = White flange standard with W reflector WF = White flange option available with C & H reflectors	61RWWPK = rotatable wall wash insert for 6" reflector – replacement part kit
Notes	Notes	Notes	Notes	Notes
	(3) Values are nominal, with specular clear reflector, other finishes and field results may vary.			

Baffle	Distribution	Finish	Flange	Accessories
Baffle	Distribution ³	Finish	Flange	Accessories
61 = 6" baffle reflector	WD = wide 65° beam angle 1.28 SC (nominal) RWW = rotatable wall wash with linear spread lens	BB = Black baffle WB = White baffle	Blank = White flange standard with BB, & WB BF = Black flange option available with BB	61RWWPK = rotatable wall wash insert for 6" reflector –replacement part kit
Notes	Notes	Notes	Notes	Notes
	(3) Values are nominal, with specular clear reflector, other finishes and field results may vary.			



HALO Commercial

HC6 | HM6 | 61 | 61PS

Order Information

IEM Reflector	Distribution	Finish	Flange	Integral Emergency
IEM Reflector	Distribution ³	Finish	Flange	Integral Emergency
61 = 6" IEM reflector for integral emergency only	ND = narrow 55° beam angle 0.97 SC MD = medium 60° beam angle 1.10 SC WD = wide 65° beam angle 1.28 SC	C = Specular clear H = Semi-specular clear W = White	Blank = Polished flange standard with C & H reflectors Blank = White flange standard with W reflector WF = White flange option available with C & H reflectors	IEM = Reflector for integral emergency only
Notes	Notes	Notes	Notes	Notes
	(3) Values are nominal, with specular clear reflector, other finishes and field results may vary.			

IEM Baffle	Distribution	Finish	Flange	Integral Emergency
IEM Baffle	Distribution ³	Finish	Flange	Integral Emergency
61 = 6" IEM baffle reflector for integral emergency only	WD = wide 65° beam angle 1.28 SC (nominal)	BB = Black baffle WB = White baffle	Blank = White flange standard with BB, & WB BF = Black flange option with BB	IEM = Reflector for integral emergency only
Notes	Notes (3) Values are nominal, with specular clear reflector, other finishes	Notes	Notes	Notes
	(3) values are nominal, with specular clear reflector, other missies and field results may vary.			

Reflector	Distribution	Finish	Flange
Reflector	Distribution ³	Finish	Flange
61PS = 6" non-conductive polymer 'dead front' conical reflector ⁴	MD = medium 60° beam angle 1.10 SC (nominal)	W = White	Blank = White flange standard with W reflector
Notes	Notes	Notes	Notes
(4) 61PS reflector is for Non-IC environment only, and up to 3000 lumens only.	(3) Values are nominal, with specular clear reflector, other finishes and field results may vary.		



HALO Commercial

HC6 | HM6 | 61 | 61PS

Product Specifications

Housing Frame

- Boat shaped galvanized steel plaster frame with adjustable plaster lip
- Accommodates 1/2" to 1-1/2" thick ceilings
 Installs in new construction or from below the
- finished ceiling (non-accessible) for remodeling (with mounting bars removed)
- Provided with two remodel clips to secure the frame to the ceiling

Universal Mounting Bracket

- Adjusts 2" vertically from above and below the ceiling
- Use with the included mounting bars or with 1/2" Electric Metallic Tube (EMT)
- Removable to facilitate remodeling installation from below the finished ceiling

Mounting Bars

- Captive pre-installed No Fuss[™] mounting bars lock to T-grid with screwdriver or pliers
- Centering detents allow for consistent positioning of fixtures

LED Module

- Proximity phosphors over chip on board LEDs provide a uniform source with high efficiency and no pixilation
- Available in 80 or 90 color rendering index (CRI)
- Color accuracy within 3 SDCM provides color consistency and uniformity
- 90 CRI option: R9>50 (refer to chromaticity information for details)
- Available in 2700K, 3000K, 3500K and 4000K correlated color temperature (CCT)
- Lumen options include 1,000, 1,500, 2,000, 3,000 and 4,000 lumens (nominal)
- Passive thermal management achieves 60,000 hours at 70% lumen maintenance (L70) in insulated ceilings (IC) and non-IC applications
- Integral diffuse lens provides visual shielding
- Integral connector allows quick connection to housing flex

Reflector

- Self-flanged aluminum reflectors available in narrow, medium or wide distribution patterns
- Medium distribution polymer non-conductive matte white reflector may be used to meet local codes for 'dead front' applications (Non-IC, 3,000 lumens max.)
- Wall wash reflector features a rotatable linear spread lens for alignment of vertical illumination
- Reflectors attach to LED module with three speed clamps
- · Available in multiple painted or plated finishes

Reflector/Module Retention

• Reflector/module assembly is securely retained in the housing with two torsion springs

Driver

- Field-replaceable constant current driver provides low noise operation
- Universal 120-277VAC 50/60Hz input standard
- 347VAC 50/60Hz input option (Canada only)
- Continuous, 1% to 100% dimming with 0-10V analog control
- Optional low-voltage DC driver for use with Distributed Low Voltage Power (DLVP) system
- Distributed Low Voltage Power (DLVP) system combines power, lighting and controls with ease of installation (refer to DLVP Design Guide at www.cooperlighting.com for details)

Emergency Option

- Provides 90 minutes of standby lighting, meeting most life safety codes for egress lighting
- Available with integral or remote charge indicator and test switch
- Available Self-Test (self-diagnostic) with remote charge indicator and test switch

Connected Lighting System Options

Two WaveLinx connected systems to choose. Summary information provided below, refer to WaveLinx system specifications and application guides for details.

WaveLinx Wireless System Tilemount Sensor Kit

 WaveLinx Wireless WTA tile mount sensor kit offers daylight dimming, PIR motion sensing, scene and zone configuration, automatic commissioning; and optional RLTS - Real Time Location Services available.

WaveLinx Lite System Tilemount Sensor Kit

 WaveLinx Lite WTK tile mount sensor kit offers daylight dimming and PIR motion sensing, scene and grouping configuration.

WaveLinx Tilemount Kits Application

- The WTA and WTK tilemount kits include a control module mounted on the luminaire junction box via 1/2" knock-out, and a tilemount sensor on 54-inch whip; for ceiling installation by direct-mount spring clips or via mounting bracket in octagon ceiling boxes.
- The WTA and WTK tilemount kits may be ordered as factory installed on the luminaire, or ordered separately as a field installed accessory kit.

Junction Box

- · Galvanized steel junction box
- 20 in³ internal volume excluding voltage barrier
 - 25 in³ internal total volume
 - Voltage barrier for 0-10V dimming wires (occupies one 1/2" pry-out space)
 - Listed for eight #12 AWG (four in, four out) 90°C conductors and feed-thru branch wiring
 - Three 1/2" and two 3/4" trade size pry-outs available
 - Three 4-port push wire nuts for mains voltage with 1-port for fixture connection

Compliance

- cULus damp and wet location listed in protected ceilings
- IP20 Above finished ceiling; IP65 Below finished ceiling
- Non-Insulated ceiling (Non-IC) rated for 3,000 and 4,000 lumen models (insulation must be kept 3" from top and sides)
- Insulated ceiling (IC) rated for 1,000, 1,500 and 2,000 lumen models and suitable for direct contact with air permeable insulation* (IC models are also suitable for Non-IC installations)
- Airtight per ASTM-E283-04
- Suitable for use in clothes closets when installed in accordance with the NEC 410.16 spacing requirements
- EMI/RFI emissions FCC CFR Title 47 Part 15 Class A at 120/277V
- · Contains no mercury or lead and RoHS compliant
- Photometric testing completed in accordance of IES LM-79-08
- Lumen maintenance projection in accordance of IES LM-80-08 and TM-21-11
- 1,000, 1,500 and 2,000 lumen, 90 CRI, ICAT models may be used to comply with State of California Title 24 residential code, per JA8 certification standards
- May be used to comply with State of California Title 24 non-residential code as a dimmable LED luminaire
- ENERGY STAR® certified, reference certified light fixtures database
 *Not for use in direct contact with spray foam insulation, consult NEMA LSD57-2013

Warranty

 Five year limited warranty, consult website for details. www.cooperlighting.com/legal



Photometric Data




NARROW DISTRIBUTION - SPECULAR CLEAR FINISH, 2000 LUMEN MODEL, 80 CRI, 3500K



COOPER

Lighting Solutions



C	CONE OF LIGHT				
МН	FC	L	w		
5.5'	64.9	5.2	5.2		
7'	40	6.8	6.8		
8'	30.7	7.6	7.6		
9'	24.2	8.6	8.6		
10'	19.6	9.6	9.6		
12'	13.6	11.6	11.6		

CANDEL	A TABLE			
Degrees Vertical	Candela			
0	1962			
5	1962			
15	1975			
25	1434			
35	671			
45	112			
55	13			
65	3			
75	3			
85	0			
90	0			

ZONAL LUMEN SUMMARY				
Zone	Lumens	% Fixture		
0-30	1385	72.1		
0-40	1796	93.5		
0-60	1915	99.7		
0-90	1920	100		
90-180	0	0		
0-180	1920	100		

LUMINANCE				
Average Candela Degrees	Average 0° Luminance			
45	8706			
55	1223			
65	337			
75	551			
85	0			

662

551

0

65 75

85

MEDIUM DISTRIBUTION - SPECULAR CLEAR FINISH, 2000 LUMEN MODEL, 80 CRI, 3500K


MEDI	UM (60° BEAM*)	CANDL	EPOWER DISTRIBUTION	C	ONE O	LIGH	т	CANDE	A TABLE	ZONAL	LUMEN SI	JMMARY
Test Number	P286170		Downlight			т	-	Degrees Vertical	Candela	Zone	Lumens	% Fixture
Housing	HC620D010		900	0	₀/i∖	 D	,	0	1642	0-30	1387	70.8
riousing	110020200010				$/ \pm $			5	1660	0-40	1821	93
Module	HM612835	475	750		\subset	⊥ (-	15	1854	0-40	1021	93
Reflector	61MDC		$ \setminus \setminus \vee \vee $					25	1576	0-60	1951	99.6
			$ \rangle X \setminus \langle \rangle$	MH	FC		W	35	699	0-90	1959	100
Lumens	1959 Lm	950	60°	5.5'	55.2	5.8	5.8	45	120			
Efficacy	97.9 Lm/W			7'	34.1	7.6	7.6	55	15	90-180	0	0
SC	1.10	1425		8'	26.1	8.6	8.6	65	5	0-180	1959	100
UGR	11.8		45°					75	3			
				9'	20.6	9.6	9.6	85	0		LUMIN	ANCE
		1900	15° 30°	10'	16.7	10.8	10.8	90	0	Γ	Average	Average 0°
			· · · · · · · · · · · · · · · · · · ·	12'	11.6	13	13		,		Candela Degrees	Luminance
											45	9236
											55	1462
										-		

PS517016EN page 5

HC6 | HM6 | 61 | 61PS

WIDE DISTRIBUTION - SPECULAR CLEAR FINISH, 2000 LUMEN MODEL, 80 CRI, 3500K





CONE OF LIGHT						
мн	FC	L	W			
5.5'	44.3	7	7			
7'	27.4	8.8	8.8			
8'	21	10.2	10.2			
9'	16.6	11.4	11.4			
10'	13.4	12.6	12.6			
12'	9.3	15.2	15.2			

CANDEL	CANDELA TABLE				
Degrees Vertical	Candela				
0	1341				
5	1349				
15	1466				
25	1642				
35	877				
45	201				
55	28				
65	5				
75	2				
85	0				

0

90

ZONAL LUMEN SUMMARY				
Zone	Lumens	% Fixture		
0-30	1282	62.7		
0-40	1835	89.7		
0-60	2037	99.6		
0-90	2045	100		
90-180	0	0		
0-180	2045	100		

LUMI	LUMINANCE					
Average Candela Degrees	Average 0° Luminance					
45	15614					
55	2676					
65	662					
75	530					
85	0					

*Value are nominal with specular clear reflectors, other finishes and field results may vary. SC = Spacing Criteria UGR = Unified Glare Rating

Photometric Multipliers (Nominal Lumen Values)

1000 Lumen	1500 Lumen	2000 Lumen	3000 LUMEN	4000 LUMEN
0.52	0.72	1.00	1.44	2.02

Multipliers for relative lumen values with other series models.

Color Finish Multipliers

Finish code	С	Н	W/WB	BB
Finish	Specular Clear	Semi-Specular	Matte White White Baffle	Black Baffle
Multiplier	1.00	0.91	0.92	0.84

Multipliers for relative lumen values with other color finishes.

CCT Multipliers - 80CRI

2700K	3000K	3500K	4000K
0.93	0.95	1.00	1.05

Multipliers for relative lumen values with other series color temperatures.


CCT Multipliers - 90CRI


2700K	3000K	3500K	4000K
0.75	0.82	0.90	0.89

Multipliers for relative lumen values with other series color temperatures.



WALL WASH DISTRIBUTION - SPECULAR CLEAR FINISH, 2000 LUMEN MODEL, 80 CRI, 3500K





CANDEL	A TABLE
Degrees Vertical	Candela
0	882
5	890
15	910
25	854
35	665
45	431
55	270
65	161
75	74
85	10
90	0

ZONAL	ZONAL LUMEN SUMMARY						
Zone	Lumens	% Fixture					
0-30	696	38.7					
0-40	1079	60					
0-60	1629	90.6					
0-90	1798	100					
90-180	0	0					
0-180	1798	100					

LUMINANCE				
Average Candela Degrees	Average 0° Luminance			
45	33399			
55	25825			
65	20832			
75	15653			
85	6416			

MULTIPLE UNIT FOOTCANDLES							
	2.5' from wall (Distance from fixture along 3					5' from w e from fixtu 4 '')	
1	18.8	16.6	18.8		17.5	10.7	17.5
2	29.5	29.2	29.5		26.8	20.9	26.8
3	29	29.8	29		26	22.9	26
4	23.7	25.3	23.7		21	20.5	21
5	17.4	19.2	17.4		15.4	16.3	15.4
6	12.5	13.7	12.5		11.1	12.2	11.1
7	9.1	9.8	9.1		8.1	9	8.1
8	6.7	7.1	6.7		6.1	6.7	6.1
9	5	5.3	5		4.6	5	4.6
10	3.8	4	3.8		3.5	3.8	3.5

SC = Spacing Criteria, nominal for specular clear reflector, other finishes and field results may vary.

SINGLE UNIT FOOTCANDLES							
2.5' from wall (distance from fixture along wall) ●							
1	16.8	12	5.4	2	0.7	0.2	0.1
2	24.7	19.2	10.5	4.9	2.2	1	0.5
3	22.8	18.6	11.4	6.2	3.2	1.7	0.9
4	17.5	15	10.3	6.2	3.6	2	1.2
5	11.9	10.7	8.2	5.5	3.4	2.1	1.3
6	8	7.4	6.1	4.5	3.1	2	1.3
7	5.5	5.2	4.5	3.6	2.6	1.9	1.3
8	3.9	3.7	3.3	2.8	2.2	1.6	1.2
9	2.8	2.7	2.5	2.2	1.8	1.4	1.1
10	2.1	2	1.9	1.7	1.5	1.2	0.9

Photometric Multipliers (Nominal Lumen Values)

1000 Lumen	1500 Lumen	2000 Lumen	3000 Lumen	4000 Lumen
0.52	0.72	1.00	1.44	2.02

Multipliers for relative lumen values with other series models.

Color Finish Multipliers

Finish code	С	Н	W/WB	BB
Finish	Specular Clear	Semi-Specular	Matte White White Baffle	Black Baffle
Multiplier	1.00	0.91	0.92	0.84

Multipliers for relative lumen values with other color finishes.

CCT Multipliers – 80CRI

2700K		3500K	4000K
0.93	0.95	1.00	1.05

Multipliers for relative lumen values with other series color temperatures.

CCT Multipliers – 90CRI

2700K	3000K	3500K	4000K
0.75	0.82	0.90	0.89

Multipliers for relative lumen values with other series color temperatures.




PS517016EN page 7 January 4, 2022 2:53 PM

HC6 | HM6 | 61 | 61PS


Energy & Performance Data


COLOR METRICS - TM-30-15 & CRI/CIE (3500K)



* Color values are based on 61WDWB reflector, other finishes and field results may vary.

TM-30-1	Rf = 8	4.7
1101-30-1	5 Rg = 9	95.7
CRI/CIE	Ra = 8	35.2
	R9 =	16.9
	-	
2700K 3000K	3500K	4000K
_		
55°	60°	65°
narrow	medium	wide
No	ominal Beam	า





Rf = 90.1

* Color values are based on 61WDWB reflector, other finishes and field results may vary.

Series	1000	umen			
Input Voltage 120-277VAC	120V	277V			
Input Current (A)	0.085	0.042			
Input Power (W)	10.1	10.9			
In-rush Current (A)	0.644	1.95			
In-rush Duration (ms)	0.125	0.24			
THDi (%)	8.6	15.6			
PF: ≥ 0.90					
(Nominal input 120-277VAC & 100% of rated output power)					
Minimum starting temperature -30°C (-22°F)*					
Sound Rating: Class A standards					
Series 3000 lumen					
Input Voltage 120-277VAC	120V	277V			

Series	1500	lumen			
Input Voltage 120-277VAC	120V	277V			
Input Current (A)	0.119	0.055			
Input Power (W)	14.2	14.9			
In-rush Current (A)	0.212	0.85			
In-rush Duration (ms)	0.28	0.32			
THDi (%)	7.8	16.3			
PF:	PF: ≥ 0.90				
(Nominal input 120-277VAC & 100% of rated output power)					
Minimum starting temperature -30°C (-22°F)*					
Sound Rating: Class A standa	rds				

Series	2000	lumen				
Input Voltage 120-277VAC	120V	277V				
Input Current (A)	0.176	0.082				
Input Power (W)	21.1	21.4				
In-rush Current (A)	0.588	0.624				
In-rush Duration (ms)	0.3	0.38				
THDi (%)	8.8	11.2				
PF:	:: ≥ 0.90					
(Nominal input 120-277VAC & 100% of rated output power)						
Minimum starting temperature -30°C (-22°F)*						
Sound Rating: Class A standa	Sound Rating: Class A standards					


Series	3000	lumen	Series	4000	lumen
Input Voltage 120-277VAC	120V	277V	Input Voltage 120-277VAC	120V	277V
Input Current (A)	0.228	0.102	Input Current (A)	0.345	0.15
Input Power (W)	27.2	27	Input Power (W)	41.3	40.7
In-rush Current (A)	0.898	1.7	In-rush Current (A)	1.05	2.23
In-rush Duration (ms)	0.36	0.38	In-rush Duration (ms)	0.32	0.34
THDi (%)	9.7	9.3	THDi (%)	10.06	14.01
PF:	≥ 0	.90	PF:	≥ 0	.90
(Nominal input 120-277VAC & 100% of rated output power)			(Nominal input 120-277VAC & power)	100% of rate	d output
Minimum starting temperature -30°C (-22°F)*			Minimum starting temperature	e -30°C (-22°	F)*
Sound Rating: Class A standards			Sound Rating: Class A standards		

Notes: * Emergency Battery packs are rated for a minimum starting temperature of 0°C.



HALO Commercial

Connected Systems





120-277 VAC 3A dov

nlights with 0-10V control


(((19)))


(((1)))

Dimensional and Mounting Details

NEW CONSTRUCTIONS - HIGH LUMEN 3000 AND 4000 LUMEN







High Lumen (3000 & 4000 Lumens)

Low Lumen (1000, 1500 & 2000 Lumens)*

Distribution	Max. Module Height	Trim Height	LED Height
Narrow	6.6"	3.4"	3.8"
Medium	6.7″	3.5"	3.9"
Wide	6.5″	3.3"	3.7″
Baffle	6.5″	3.3″	3.7"

 Height
 Max. Module Height
 Trim Height
 LED Height

 3.8"
 4.5"
 3.4"
 3.8"

 3.9"
 4.6"
 3.5"
 3.9"

 3.7"
 4.4"
 3.3"
 3.7"

 3.7"
 4.4"
 3.3"
 3.7"

*Max. height w/hanger bar bracket 4.2"



© 2020 Cooper Lighting Solutions All Rights Reserved. Specifications and dimensions subject to change without notice.