



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



FMVA13LCYUNV176 93W 100-277V 5000K Yk MT Led Flood *Crouse-Hinds*

Catalog Number	FMVA13LCYUNV176
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Champ Fmva Led Floodlight, Cool White, Dimmable Driver, 3/4" Entry, 400W Equiv, Heat and Impact Resistant Glass Lens, 13000 Lumens, 143 LM/W, Die Cast Aluminum, Yoke Mount, 100-277 Vac, 108-250 VDC, 95W, 7X6 Optics
Weight per unit	32.5 (lbs/each)
Product Category	20190918152119

Descriptions

Description	93W 100-277V 5000K YK MT LED FLOOD
extra long description	CRS-H FMVA13LCY-UNV1-76 LED FLOOD C
Features	Crouse-Hinds series Champ FMVA LED floodlights are designed to provide full-spectrum, crisp, white light in Class I and Class II hazardous areas. Eleven versions of the Champ FMVA are available, ranging from 3,000 to 50,000 lumens, providing a reliable and long-life solution for a wide range of floodlighting applications. Champ FMVA LED floodlights are certified for use in NEC, CEC and IEC hazardous locations, providing a single solution for applications around the world. These floodlights are ideal for
Long Description	Eaton Crouse-Hinds series Champ FMVA LED floodlight, Cool white, Dimmable driver, 3/4" entry, 400W equiv, Heat and impact resistant glass lens, 13000 lumens, 143 lm/W, Die cast aluminum, Yoke mount, 100-277 Vac, 108-250 Vdc, 95W, 7x6 optics
Product Type	Led Flood Cool Glass Lens 100-277 Vac 108-250 VDC

Manufacturer Information

Brand	Eaton
GTIN	00662276869394
Manufacturers Part Number	FMVA13LCY-UNV1-76
UPC	662276869394

Taxonomies, Classifications, and Categories

Category Description	HAZARDOUS LOCATION LIGHTING FIXTURES
----------------------	--------------------------------------

Packaging

Carton	1
Weight Per each	32.5