

# Eaton FNM-25

Catalog Number: FNM-25

Eaton Bussmann series FNM fuse, Time-delay, 25 A, Dual, Non-indicating, Ferrule end x ferrule end, 10 kAIC at 250 Vac, Nickel-plated bronze endcap, Standard, 250 V



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Bussmann series FNM fuse	FNM-25
<b>UPC</b>	<b>EAN</b>
051712522250	5027590243124
<b>Product Length/Depth</b>	<b>Product Height</b>
0.39 in	1.44 in
<b>Product Width</b>	<b>Product Weight</b>
0.39 in	0.2 lb
<b>Warranty</b>	<b>Compliances</b>
Not Applicable	CE Marked RoHS Compliant

## Electrical rating

### Amperage Rating

25 A

### Interrupt rating

10 kAIC at 250 Vac

### Voltage rating

250 V

## Physical details

### Material

Nickel-plated bronze endcap

### Number of elements

Dual

### Packaging type

Standard

## General information

### Connection

Ferrule end x ferrule end

### Fuse indicator

Non-indicating

### Special features

Superior overload and cycling capabilities

## Resources

### Catalogs

[Bussmann series complete full line catalog no. 1007](#)

### Multimedia

[Bussmann series Fuseology](#)

### Specifications and datasheets

[Eaton Specification Sheet - FNM-25](#)

### Technical data sheets

[FNM-25~BUSS MIDGET FUSE](#)

### Technical service bulletins

[Datasheet - FNQ-30](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)