



## HCLR15 15A 600V Class CC Fast Acting Fuse

*Edison Fuses*

Catalog Number	HCLR15
Manufacturer	Edison Fuses
Description	Class CC Fuse, 15 A, 600 V Ac, Melamine (Body);Brass (End Cap) Material, 0.41 In Diameter, 1.50 In Overall Length, 0.02 LB
Weight per unit	0.0200 (lbs/each)
Product Category	Renewable & Non-Renewable

### Features

amperage rating	15
media	Yes

### Dimensions and Weight

Height	0.406
Length	1
Width	0.406

### Descriptions

Description	15A 600V CLASS CC FAST ACTING FUSE
extra long description	EFSE HCLR15 UL CLASS CC FAST ACTING
Features	Edison offers a complete line of Class CC fuses to meet your circuit and equipment protection needs. These branch circuit rated compact fuses rated 600v, and delivering 200,000a IR Vac Sym provide excellent protection in the smallest package of any UL class of fuses. Choose from our EDCC time-delay fuses for your small horsepower motor circuits, our HCLR fast-acting for your non-inductive lighting and resistance heating loads or our HCTR time-delay fuses for your small control transformer protection.
Special Features	Rejection Style

### Manufacturer Information

Brand	Eaton
GTIN	00782634420705
Manufacturers Part Number	T626-HCLR15
UPC	782634420705

### Taxonomies, Classifications, and Categories

Category Description	MIDGET FUSES
Type	FUSE

### Packaging

Carton	1
Package	10
Weight Per each	0.02



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1732 South Business 287  
75110-0000, TX Corsicana  
Phone: 903-872-9696  
Fax: 903-872-9980

## Uses, Certifications, and Standards

Application  
standard

Datacenters - Facilities: Critical Power

UL Listed, CSA Certified, CE Marked, RoHS Compliant