



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **G572046G050 20000BTU, 460V Encl A/C** *Hoffman Enclosures, Inc.*

Catalog Number	G572046G050
Manufacturer	Hoffman Enclosures, Inc.
Description	Spectracool Indoor/Outdoor G57, 20000BTU 460V, LT Gray, Steel
Weight per unit	180.0 (lbs/each)
Product Category	Enclosure Air Conditioners

### **Features**

Material	MILD STEEL
nominal voltage	460
Number of Phases	3
Phase	3 Ph
Voltage Rating	400/460 V

### **Material, Color, and Finish**

Color	Light Gray
Color Code	RAL 7035
Finish	Powder Coated

### **Descriptions**

Description	20000BTU,460V ENCL A/C
extra long description	NVENT HOF G572046G050 20000 BTU,460
Features	SpectraCool Air Conditioners are available in three sizes that offer a broad range of cooling capacities and configurations. These units deliver reliable enclosure cooling in demanding environments that features reliable design, clean appearance, easy installation, and a filterless design.
Long Description	SpectraCool Indoor/Outdoor G57, 20000BTU 460V, Lt Gray, Steel
Product Type	20000 Btu, 460V, 50/60 HZ, 3PH

### **Manufacturer Information**

Brand	Nvent Hoffman
GTIN	00783510205171
Manufacturers Part Number	G572046G050
UPC	783510205171

### **Taxonomies, Classifications, and Categories**

Category Description	Residential HVACR Equipment single phase
Type	Air Conditioners

### **Packaging**

Carton	1
Weight Per each	180



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application	Power Distribution; Controls and Drives
Frequency Rating	50/60 Hz
nema rating	4 Watertight
Operating Temperature	50-131