



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GALNIP12XCL 1/2XCL RGD Nip

Robroy/Ecn Korns

Catalog Number	GALNIP12XCL
Manufacturer	Robroy/Ecn Korns
Description	Conduit Nipple, Steel Material; Galvanized Finish; 1-1/8 Inch; UL 6, Csa C22.2 Approval; Ansi C80.1, Nema Applicable Standard; 25 Per Carton Standard Package; 1/2 Inch Trade Size; Threaded End Type; Galnip Model
Weight per unit	0.0600 (lbs/each)
Product Category	Steel

Features

Applicable Standard	ANSI C80.1, NEMA
End Type	THREADED
Material	Steel

Material, Color, and Finish

Finish	Galvanized
--------	------------

Dimensions and Weight

Length	1-1/8 INCH
--------	------------

Descriptions

Commodity Description	ELBOWS-COUPINGS-NIPPLES - STEEL
Description	1/2XCL RGD NIP
extra long description	MALE THREADED, CLOSE TYPE; HOT DIP GALVANIZED STEEL MATERIAL; 1-1/8 INCH; IMC/RIGID CONDUIT USED ON; UL (CANADA AND US), UL 6, CSA C22.1/C22.2, NOM APPROVAL; 0.84 INCH DIAMETER; 25 PER CARTON STANDARD PACKAGE; 1/2 INCH TRADE SIZE; APPLICATION INDOOR/OUTDOOR, HAZARDOUS AND NON-HAZARDOUS LOCATION; APPLICABLE STANDARD ANSI/NFPA 70, NEC 344, ISO 9001; GALNIP MODEL
Long Description	CONDUIT NIPPLE, STEEL MATERIAL; GALVANIZED FINISH; 1-1/8 INCH; UL 6, CSA C22.2 APPROVAL; ANSI C80.1, NEMA APPLICABLE STANDARD; 25 PER CARTON STANDARD PACKAGE; 1/2 INCH TRADE SIZE; THREADED END TYPE; GALNIP MODEL
Product Type	Conduit Nipple

Manufacturer Information

Brand	ECN-KORNS
GTIN	00784011004010
Manufacturers Part Number	GALNIP1/2XCL
Model	GALNIP
UPC	784011004010



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description RIGID NIPPLES

Trade Size

Trade Size 1/2 INCH

Packaging

Carton 1

Package 25

Standard Package 25 PER CARTON

Weight Per each 0.06

Uses, Certifications, and Standards

Approval UL 6, CSA C22.2