

HU11

Value LED Undercabinet


HALO



halolighting.com

# HU11 Value LED undercabinet





**HALO® introduces the HU11 to address your LED undercabinet and task lighting needs.**

Ideal for task, accent, office, cove, utility and display lighting, the HALO Undercabinet low-profile design delivers maximum energy savings and long life. The integrated driver allows 120V direct to the fixture for easy installation. Available in multiple lengths, the HU11 can be configured to fit almost anywhere. The HU11 has smooth dimming down to 5% using a TRIAC (leading edge) or ELV (trailing edge) dimmer. Connector cables, in a variety of different lengths, make it easy to link one unit to another. Each unit features an integrated on-off switch.

# Value LED undercabinet


## Features

- SeleCCTable™ color temperature for flexible lighting effects and applications (2700K, 3000K or 4000K)
- Sleek and seamless <1" profile
- Delivers up to 60 Lumens per Watt
- 90 CRI
- Dimmable down to 5% with select 120V dimmers
- Multiple wiring options including flexible conduit, romex or plugin
- Back wire option for increased space utilization\*\*\*
- 120V input
- Lumen maintenance (L70) at 50,000 hours
- 5-year warranty
- Damp location listed




## Selectable CCT


Three position external seleCCTable color temperature switch allows users to choose between 2700K, 3000K, and 4000K and adjust to their lighting needs.



## Dimensions



Size	9 in. Nominal	18 in. Nominal	24 in. Nominal	36 in. Nominal	48 in. Nominal
Length "L"	8.98" [228.1mm]	16.55" [420.4mm]	23.98" [609.1mm]	32.44" [824mm]	47.18" [1,198.4mm]



## Energy Data

	Lumens	120V Input Watts
9" Fixture	300	4.5
18" Fixture	560	8.0
24" Fixture	785	11.0
36" Fixture	1125	15.5
48" Fixture	1540	21.0

Power Factor	> 0.9
THD	< 20%
Color Temperature	2700K 3000K 4000K
Color Rendering Index	90
Nominal Lumens/Ft.	300



## Ordering Information

Sample Number: **HU1118DSP** (18" dimmable fixture, 90 CRI, selectable color temperature, White finish)

Family	Length	Dimming	Color Temp	Finish
<b>HU11</b> = Halo integrated undercabinet	<b>09</b> = 9" <b>18</b> = 18" <b>24</b> = 24" <b>36</b> = 36" <b>48</b> = 48"	<b>D9</b> = Dimmable	<b>S</b> = Selectable (2700K, 3000K, 4000K)	<b>P</b> = White <b>MB</b> = Matte Black

## Connectors & Accessories



3" Daisy Chain Connector  
HU101



6" Daisy Chain Connector  
HU102



12" Daisy Chain Connector  
HU1010



18" Daisy Chain Connector  
HU1011



24" Daisy Chain Connector  
HU103



120" Daisy Chain Connector  
HU104



48" Power Cord - 120V only  
HU115



1-1/2" Male-to-Male Connector  
HU107



Splice Box  
HU109



Master Switch  
HU10MS



Finish: **P** = White; **MB** = Matte Black

Example: HU101P = 3" Daisy Chain Connector, White



## Wiring Flexibility

The HU11 has the ability to bring flexible conduit or armored cable directly into the fixture from the back to allow for increased space savings. Conduit connector and armored cable strain relief hardware is included in each fixture. In addition, users can also utilize the various available plug in connectors for 120V applications.



## **Cooper Lighting Solutions**

1121 Highway 74 South  
Peachtree City, GA 30269  
P: 770-486-4800  
www.halolighting.com

## **Canada Sales**

5925 McLaughlin Road  
Mississauga, Ontario L5R 1B8  
P: 905-501-3000  
F: 905-501-3172

## **Our Lighting Product Lines**

Ametrix  
AtLite  
Corelite  
Ephesus  
Fail-Safe  
HALO  
HALO Commercial  
Invue  
io  
IRiS  
Lumark  
Lumière  
McGraw-Edison  
Metalux  
MWS  
Neo-Ray  
Portfolio  
RSA  
Shaper  
Streetworks  
Sure-Lites

## **Our Controls Product Lines**

Fifth Light Technology  
Greengate  
iLight (International Only)  
iLumin  
Zero 88

## **Connected Lighting Systems**

Distributed Low-Voltage Power  
HALO Home  
iLumen Plus  
LumaWatt Pro  
WaveLinx

## **Cooper Lighting Solutions**

1121 Highway 74 South  
Peachtree City, GA 30269  
P: 770-486-4800  
www.halolighting.com

© 2020 Cooper Lighting Solutions  
All Rights Reserved  
Printed in USA  
Publication No. BR518065EN  
February 2020

Products, specifications and  
compliances are subject to  
change without notice.

Cooper Lighting Solutions is a  
registered trademark.

All other trademarks are property  
of their respective owners.

