



GAR1929

by Burndy
Catalog ID: GAR1929

Prop 65 Notice

Mechanical Grounding Connector, Cable to Rod or Pipe, 2/0 AWG (Sol.) - 250 kcmil, 2-1/2" to 2-7/8" Rod, 2-1/2" Pipe, Bright Dipped.

Features: High Copper Alloy Ground Connector For Joining A Range Of Cable, Parallel Or At Right Angles To Rod Or Tube, Especially Good For Fence Posts, High Copper Alloy Cast Body With DURIMUM U-Bolts, Nuts And Lockwashers, Permit Entire Connection To Be Buried In Ground Or Concrete Without Danger Of Corrosion, One-Wrench Installation, UL467 Listed, Acceptable For Direct Burial, Ground Rod Size: 2-1/2 - 2-7/8 IN, Tube (ips) Size: 2-1/2 IN, Height: 5 IN, Width: 4-1/4 IN, Installation Torque: 240 IN-LB

Product Details

General

Application	For Joining A Range Of Cable, Parallel Or At Right Angles To Rod Or Tube, Direct Burial Cable, Fence Post
Installation Torque Recommended Run in-lb	240 Lb-in
Installation Torque Recommended in-lb	240 LBS/in
Material	Copper
Material - Hardware	DURIMUM™ Silicon Bronze
Plated	N
Plating Type	Bright Dipped
Sub Brand	MECHANICAL CONNECTOR
Type	GAR
U Bolt Type	266
UPC	781810236000
UPC 12 Digit	7818102360000

Dimensions

Dimension - B Length inch	3.25 in
Dimension - Height fraction	5 in
Dimension - Height inch	5.00 in
Dimension - L Length Overall mm	46 mm
Dimension - Length Overall inch	1.81 in
Dimension - Outside Diameter inch	2.88 in
Dimension - Width fraction	4-1/4 in
Dimension - Width inch	4.19 in
Dimension - Width mm	106 mm

Conductor Related

Conductor - Copper Solid Size	2/0 AWG
Conductor - Copper Solid Size Range	2/0 AWG-4/0 AWG
Conductor - Copper Str Size	250 kcmil

Conductor - Copper Str Size Range	1/0 -250 kcmil
Conductor - Copper Tube Std Size	2 1/2 IPS IPS
Conductor - Copper Tube Std Size Range	2 1/2 IPS IPS
Conductor - Pipe or Round Tube Size Range	2-1/2 in
Conductor - Rod Size	2.5 in-2.88 in
Conductor - Rod Size Range	2 1/2 in-2 7/8 in
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size • CU Tube Std-Size • Rod-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)