



GC2929CT, Mechanical Grounding Connector, 2 Cables to Bar

By Burndy
Catalog # [GC2929CT](#)

Cast CU Alloy Cable Tray Ground Clamp, 2/0 Str.-250 kcmil, Tin-plated.



Application

For Direct Burial Applications In Concrete Or Earth And For Used With Aluminum Or Galvanized Steel Cable Tray

General

EU RoHS Indicator	Yes
Installation Torque	240 LBS/in
Recommended in-lb	
Material	Copper Alloy
Plated	Y
Plating Type	Tin
Sub Brand	MECHANICAL CONNECTOR
Type	GC-CT
UPC	781810220580
UPC 12 Digit	7818102205800

Dimensions

Dimension - B Length inch	1.12 in
Dimension - Cross Flats inch	0.56 in
Dimension - Height inch	2.20 in
Dimension - Width inch	1.98 in
Dimension - Width mm	50 mm

Conductor Related

Conductor - AL Str Size	2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil
Conductor - AL Str Size Range	2/0 AWG-250 kcmil
Conductor - Copper Solid Size	4/0 AWG
Conductor - Copper Solid Size Range	4/0 AWG
Conductor - Copper Str Size	2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil
Conductor - Copper Str Size Range	2/0 AWG - 250 kcmil

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [3D Models - GC2929CT_MODEL-STEP](#)
- [3D Models - GC2929CT_MODEL-PDF](#)
- [3D Models - GC2929CT_MODEL-IGES](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Sales Drawings - sc082752-01](#)



A proud member of the Hubbell Family.