



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GHB1020 20A GHB 1P BKR *Eaton Corp*

Catalog Number	GHB1020
Manufacturer	Eaton Corp
Description	Eaton Series C Complete Molded Case Circuit Breaker, G-Frame, GHB, Complete Breaker, Fixed Thermal, Fixed Magnetic Trip Type, Single-Pole, 20A, 277 Vac, 125 VDC, 14 Kaic At 277 Vac, 50/60 HZ, 24
Weight per unit	0.6000 (lbs/each)
Product Category	1 Pole

Features

Current Rating	20 A
dimensions	2.6300 IN X 1.0000 IN X 4.0000 IN
frame	G
interrupt rating	14 kAIC at 277 Vac
media	Yes
Poles	Single-pole
Voltage Rating	277 Vac, 125 Vdc

Descriptions

Description	20A GHB 1P BKR
extra long description	ETN GHB1020BP24 20A GHB 1P CB 4 KEY
Features	Experience the superior quality of the Eaton Series C Molded Case Circuit Breaker. The Series C circuit breaker is ideal for panelboards, switchboards, motor control centers, and busway applications. Choose from a premier selection of trip units including thermal magnetic, electronic, and magnetic only switches. Available for systems up to 600 VAC or 250 VDC with current ratings up to 800A.
Long Description	Eaton Series C complete molded case circuit breaker, G-frame, GHB, Complete breaker, Fixed thermal, fixed magnetic trip type, Single-pole, 20A, 277 Vac, 125 Vdc, 14 kAIC at 277 Vac, 50/60 Hz, 24
Product Type	20A GHB 1P CB 4 Key Operated Attachment

Manufacturer Information

Brand	Eaton
GTIN	00786679022030
Manufacturers Part Number	GHB1020BP24
UPC	786679022030



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description PANELBOARD BRANCH BREAKERS
Type Molded case circuit breaker

Availability

Status Inactive

Packaging

Carton 1
Weight Per each 0.6

Uses, Certifications, and Standards

Application Elec Assemblies, Panels & EOEM - Electrical Assemblies and
EOEMs - Other
standard UL Listed,Federal Specifications Classification W-C375B