



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ICN2S54T35M (2) F54T5/Ho 120-277V Elec Bal

Advance By Signify

Catalog Number	ICN2S54T35M
Manufacturer	Advance By Signify
Description	No Matter What The Conditions Require, Operating At A Variety Of Line Voltages Between 120V to 480V, Whether Located In High Ambient Temperature Environments (Requiring A 90° C Rating) or Not, Our Family Of Philips Advance Centium Ballasts Are Ideal For A Wide Variety Of Applications.
Weight per unit	1.0 (lbs/each)
Product Category	Electronic Linear Fluorescent

Features

amperage rating	0.83-0.36
ANSI Code	N/A
Ballast Factor	1
dimmable	Non Dimmable
Lamp Type	Fluorescent
Minimum Starting Temperature	5
Number of Lamps	2
Power Factor	0.98
start type	Programmed
total harmonic distortion	<=10
Voltage Rating	120-277
Wattage	98

Material, Color, and Finish

Color	White
-------	-------

Dimensions and Weight

Height	4.17
Length	55.79
Width	4.65

Descriptions

Description	(2) F54T5/HO 120-277V ELEC BAL
extra long description	ADV 501684 ELE BALLAST (2) F54T5/HO
Long Description	No matter what the conditions require, operating at a variety of line voltages between 120V to 480V, whether located in high ambient temperature environments (requiring a 90° C rating) or not, our family of Philips Advance Centium ballasts are ideal for a wide variety of applications.
Product Type	Ele Ballast (2) F54T5/Ho 120-277V
Special Features	IntelliVolt 120-277V, Series Lamp Operation, Connector



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Signify Electronics
GTIN	00781087131794
Manufacturers Part Number	ICN2S54T35M
UPC	781087131794

Taxonomies, Classifications, and Categories

Category Description	ELECTRONIC BALLAST
Type	ELECTRONIC

Packaging

Carton	1
Weight Per each	1

Uses, Certifications, and Standards

Application	Commercial
Frequency Rating	50to60
Mounting	13.78
standard	CSA certificate;UL certificate;RoHS Compliant