



Centium T8 Instant Start

CENTIUM ICN3P32N35I

Reliable and energy efficient Philips Advance's Centium commercial grade specifications, plus added benefits of lamp striation reduction technology.

Product data


| General Information | | Wire Striplength | |
|-------------------------------|------------------------|--|--------------------------|
| Lamp Type | F32T8 | Wire Striplength | 0.50/0.375 mm |
| Number of Lamps | 2/3 piece/unit | Lamp Connection | Parallel |
| Ballast Type | Electronic Fluorescent | Wire Length by Color | See data sheet |
| Base Model | ICN3P32N | Wire Gauge (Nom) | 18AWG mm |
| Suitable For Outdoor Use | Yes | Wire Type | Solid |
| Automatic Restart | Yes | Remote Wiring Configuration Allowed | Yes |
| | | Tandem Wiring Configuration Allowed | Yes |
| | | Through Wiring Configuration Allowed | Yes |
| Operating and Electrical | | Max Ballast-Lamp Distance Remote Wiring | ES = 6' / Standard = 20' |
| Input Voltage | 120 to 277 V | Max Ballast-Lamp Distance Tandem Wiring | ES = 6' / Standard = 20' |
| Input Frequency | 50 to 60 Hz | Max Ballast-Lamp Distance Through Wiring | ES = 6' / Standard = 20' |
| Total Harmonic Distortion USA | 10 % | Connector Type | No connector |
| Ignition Method | Instant Start | Temperature | |
| Crestfactor (Nom) | 1.7 | T-Case Maximum (Nom) | 70 °C |
| Ignition Time (Nom) | 0.1 s | Mechanical and Housing | |
| Ballast Factor (Nom) | 0.88 | Housing Material | Metal |
| Power Factor (Nom) | 0.98 | Housing | N |
| Input Current (Max) | 0.71 A | Housing Dimensions | 9.5" x 1.3" x 1.0" |
| Input Current (Min) | 0.31 A | Approval and Application | |
| Input Power (Nom) | 85-86 W | EMC Immunity Standard | FCC Non-Consumer |
| Rated Lamp Power | 32 W | | |
| Wiring | | | |
| Color Input Terminals | No terminals | | |
| Color Output Terminals | No terminals | | |

Centium T8 Instant Start

| | |
|----------------------------|--|
| Approval Marks | CSA certificate UL certificate CEC Listing CEE Rated NEMA Premium NOM certificate RoHS Compliant |
| Hum And Noise Level | A |
| UL Recognized | No |
| Product Data | |
| Order product name | CENTIUM ICN3P32N35I |

| | |
|--|--------------|
| EAN/UPC - Product | 781087091494 |
| Order code | 913701220201 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 10 |
| Material Nr. (12NC) | 913701220201 |
| Net Weight (Piece) | 0.441 kg |

Dimensional drawing



ELE BALLAST (3) 120-277V F32T8 120-277V

| Product | A1 | A2 | B1 | C1 |
|---------------------|---------|---------|---------|---------|
| CENTIUM ICN3P32N35I | 9.50 in | 8.90 in | 1.30 in | 1.00 in |





Centium T8 Instant Start

CENTIUM ICN3P32N35I

Reliable and energy efficient Philips Advance's Centium commercial grade specifications, plus added benefits of lamp striation reduction technology.

Product data


| General Information | | Wire Striplength | |
|-------------------------------|------------------------|--|--------------------------|
| Lamp Type | F32T8 | Wire Striplength | 0.50/0.375 mm |
| Number of Lamps | 2/3 piece/unit | Lamp Connection | Parallel |
| Ballast Type | Electronic Fluorescent | Wire Length by Color | See data sheet |
| Base Model | ICN3P32N | Wire Gauge (Nom) | 18AWG mm |
| Suitable For Outdoor Use | Yes | Wire Type | Solid |
| Automatic Restart | Yes | Remote Wiring Configuration Allowed | Yes |
| | | Tandem Wiring Configuration Allowed | Yes |
| | | Through Wiring Configuration Allowed | Yes |
| Operating and Electrical | | Max Ballast-Lamp Distance Remote Wiring | ES = 6' / Standard = 20' |
| Input Voltage | 120 to 277 V | Max Ballast-Lamp Distance Tandem Wiring | ES = 6' / Standard = 20' |
| Input Frequency | 50 to 60 Hz | Max Ballast-Lamp Distance Through Wiring | ES = 6' / Standard = 20' |
| Total Harmonic Distortion USA | 10 % | Connector Type | No connector |
| Ignition Method | Instant Start | | |
| Crestfactor (Nom) | 1.7 | Temperature | |
| Ignition Time (Nom) | 0.1 s | T-Case Maximum (Nom) | 70 °C |
| Ballast Factor (Nom) | 0.88 | | |
| Power Factor (Nom) | 0.98 | Mechanical and Housing | |
| Input Current (Max) | 0.71 A | Housing Material | Metal |
| Input Current (Min) | 0.31 A | Housing | N |
| Input Power (Nom) | 85-86 W | Housing Dimensions | 9.5" x 1.3" x 1.0" |
| Rated Lamp Power | 32 W | | |
| Wiring | | Approval and Application | |
| Color Input Terminals | No terminals | EMC Immunity Standard | FCC Non-Consumer |
| Color Output Terminals | No terminals | | |

Centium T8 Instant Start

| | |
|----------------------------|--|
| Approval Marks | CSA certificate UL certificate CEC Listing CEE Rated NEMA Premium NOM certificate RoHS Compliant |
| Hum And Noise Level | A |
| UL Recognized | No |
| Product Data | |
| Order product name | CENTIUM ICN3P32N35I |

| | |
|--|--------------|
| EAN/UPC - Product | 781087091494 |
| Order code | 913701220201 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 10 |
| Material Nr. (12NC) | 913701220201 |
| Net Weight (Piece) | 0.441 kg |

Dimensional drawing



ELE BALLAST (3) 120-277V F32T8 120-277V

| Product | A1 | A2 | B1 | C1 |
|---------------------|---------|---------|---------|---------|
| CENTIUM ICN3P32N35I | 9.50 in | 8.90 in | 1.30 in | 1.00 in |

