

e-Vision Low Wattage 20-150W

E-VISION ELE MH BAL 100W M140 120-277 50/60HZ

Low frequency electronic HID ballasts such as the Philips Advance e-Vision line constantly measure and adjust the wattage, optimizing delivery of the ceramic lamps' superior color properties. This makes ceramic metal halide operated by e-Vision ballasts the premier choice for many applications previously illuminated by either tungsten halogen or incandescent sources, such as retail lighting.

Product data

General Information	
ANSI Code	C90-M90,M140,C191
Lamp Type	100W MH
Number of Lamps	1 piece/unit
Ballast Type	Electronic HID
Base Model	IMH100BLF
Suitable For Outdoor Use	Yes
Operating and Electrical	
Input Voltage	120 to 277 V
Input Frequency	50 to 60 Hz
Max THD	15 %
Lamp Current Crest Factor (Nom)	1.8
Ignition Time (Nom)	1200 s
Ballast Factor (Nom)	1
Power Factor (Nom)	0.90
Input Current (Operating) (Max)	0.92 A
Input Current (Operating) (Min)	0.4 A


Input Power (Nom)	110-109 W
Rated Lamp Watts	100 W
Wiring	
Color Input Terminals	No terminals
Color Output Terminals	No terminals
Wire Striplength	0.50 mm
Control Wire Gauge	NA
Wire Length By Color	All leads = 11"
Wire Gauge (Nom)	18AWG mm
Wire Type	Stranded
Remote Wiring Configuration Allowed	Yes
Tandem Wiring Configuration Allowed	No
Through Wiring Configuration Allowed	No
Connector Type	No connector

e-Vision Low Wattage 20-150W

Temperature	
T-Case Maximum (Nom)	85 °C
Mechanical and Housing	
Housing Material	Metal
Housing	A-B
Housing Dimensions	4.7" x 3.6" x 1.5"
Approval and Application	
EMC Immunity Standard	FCC Non-Consumer
Approbation Marks	CSA certificate UL certificate RoHS Compliant
Sound Rating	A

UL Recognized	No
Product Data	
Order product name	E-VISION IMH100BLFM
EAN/UPC - Product	781087074947
Order code	IMH100BLFM
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	913710856302
Net Weight (Piece)	631.000 g

Dimensional drawing



Product	A1	A2	A3	A4	B1	B2	C1
E-VISION IMH100BLFM	5.5 in	4.7 in	5.2 in	2.0 in	3.6 in	2.9 in	1.5 in

E-VISION IMH100BLFM

