



## IPLD2504 250MCM-#6 4 Pole Polaris Connector Block

*Nsi Industries*

Catalog Number	IPLD2504
Manufacturer	Nsi Industries
Description	Multi-Tap Connector, #6 Awg Conductor Size, 250 MCM Conductor Size, Insulated, Plastisol Insulation Material, Copper/Aluminum Conductor Material, Black Insulation Color, 4 Conductors, -45 °C Operating Temperature, +90 °C Operating Temperature, 3.8 In Overall Length, 600 V, 0.47 LB/Ea
Weight per unit	0.4700 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	250 MCM-6 AWG
Wire Type	Class B & C

### Material, Color, and Finish

Color	Black
Finish	Plastisol Insulated
Housing Material	Aluminum

### Dimensions and Weight

Size	L=3.800 - W=2.280 - H=2.180
------	-----------------------------

### Descriptions

Description	250MCM-#6 4 POLE POLARIS CONNECTOR BLOCK
extra long description	NSI IPLD250-4 Clr 250-6AWG Insld M
Features	The Polaris IPLD250-4 4-Port Dual-Sided Connector provides the simplest solution for forming a secure connection between up to four conductors in applications including cable trays, panel boards, ducts, raceways or troughs. Sized for 250 MCM - 6 AWG wires and rated for 600V, this pre-insulated connector comes pre-loaded with an oxide inhibitor and installs faster than traditional uninsulated connector options using just a hex key and torque wrench. The aluminum-alloy body is wrapped in high-dielectric stre

### Manufacturer Information

GTIN	00662381923028
UPC	662381923028



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

520 Equity Ave  
72032-0000, AR Conway  
Phone: 501-336-8444  
Fax: 501-329-5636

## Taxonomies, Classifications, and Categories

Category Description	SPLIT BOLTS
Type	Double Sided Entry

## Packaging

Carton	6
Weight Per each	0.47

## Uses, Certifications, and Standards

Application	Wire Termination
environmental conditions	90 C
standard	UL 486A/B