

ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr. 75964-0000, TX Nacogdoches Phone: 936-569-7941 Fax: 936-560-4685



IPLD3503 350MCM-#6 3 Pole Polaris Connector Block

Nsi Industries

Catalog Number	IPLD3503
Manufacturer	Nsi Industries
Description	Multi-Tap Connector, #6 Awg Conductor Size, 350 MCM
	Conductor Size, Insulated, Plastisol Insulation Material,
	Copper/Aluminum Conductor Material, Black Insulation Color, 3
	Conductors, -45 °C Operating Temperature, +90 °C Operating
	Temperature, 3.52 In Overall Length, 600 V, 0.59 LB/Ea
Weight per unit	0.5900 (lbs/each)
Product Category	Large Terminals & Connectors
Features	
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	350 MCM-6 AWG
Wire Type	Class B & C
Material, Color, and Finish	
Color	Black
Finish	Diagtical Insulated
Housing Material	Aluminum
Dimensions and Weight	
Size	L=3.520 - W=2.410 - H=2.610
Descriptions	
Description	350MCM-#6 3 POLE POLARIS CONNECTOR BLOCK
extra long description	NCLIDI DOCA O DOLADICIDO Multi Ton
Features	The Polaris IPLD350-3 3-Port Dual-Sided Connector provides the
	simplest solution for forming a secure connection between up to
	three conductors in applications including cable trays, panel
	boards, ducts, raceways or troughs. Sized for 350 MCM - 6 AWG
	wires and rated for 600V, this pre-insulated connector comes
	pre-loaded with an oxide inhibitor and installs faster than
	traditional uninsulated connector options using just a hex key
	and torque wrench. The aluminum alloy body is wrapped in
	high-dielectric str
Manufacturer Information	
GTIN	00662381924018
UPC	662381924018



standard

ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr. 75964-0000, TX Nacogdoches Phone: 936-569-7941 Fax: 936-560-4685

Taxonomies, Classifications, and Categories		
Category Description	SPLIT BOLTS	
Туре	Double Sided Entry	
Packaging		
Carton	4	
Weight Per each	0.59	
Uses, Certifications, and Standar		
Application	Wire Termination	
environmental conditions	90 C	

UL 486A/B