



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

800 Old Boston Road
75501-0000, TX Texarkana
Phone: 903-223-6400
Fax: 903-223-6700



ISPBS20 14-2/0AWG Conn *Nsi Industries*

Catalog Number	ISPBS20
Manufacturer	Nsi Industries
Description	Submersible Connector, #14 Awg Conductor Size, 2/0 Awg Conductor Size, Insulated, Epdm Rubber Insulation Material, Aluminum Conductor Material, Black Insulation Color, 2 Conductors, -45 °C Operating Temperature, +90 °C Operating Temperature, 5.05 In Overall Length, Screw Terminal, 600 V Ac, 0.17 LB/Ea
Weight per unit	0.1700 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Number of Conductors	2
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	2/0-14 AWG
Wire Type	Class B & C

Material, Color, and Finish

Color	Black
Finish	EPDM Rubber Insulated
Housing Material	Aluminum

Dimensions and Weight

Size	L=.880 - W=5.05 - H=2.10
------	--------------------------

Descriptions

Description	14-2/0AWG CONN
extra long description	NSI ISPBS2/0 POLARIS EDGE Connector
Features	The Polaris ISPBS2/0 2-Port In-Line Entry Submersible Connector provides the simplest solution for forming a secure connection between two conductors in direct burial or temporary submersal applications with a wide range of wire sizes. Sized for 2/0 - 14 AWG wires and rated for 600V, this pre-insulated connector comes pre-loaded with an oxide inhibitor and installs faster than traditional connector options using just a hex key and torque wrench. The aluminum alloy body is wrapped in high-dielectric strengt

Manufacturer Information

GTIN	00662381787811
UPC	662381787811



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

800 Old Boston Road
75501-0000, TX Texarkana
Phone: 903-223-6400
Fax: 903-223-6700

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Submersible Pedestal Connectors

Packaging

Carton	3
Weight Per each	0.17

Uses, Certifications, and Standards

Application	Wire Termination
environmental conditions	90 C
standard	ANSI C119.4, C119.1, UL486D