

ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr. 75964-0000, TX Nacogdoches Phone: 936-569-7941 Fax: 936-560-4685



ISPBS350 12AWG-350MCM Conn *Nsi Industries*

Catalog Number	ISPBS350
Manufacturer	Nsi Industries
Description	Submersible Connector, #12 Awg Conductor Size, 350 MCM Conductor Size, Insulated, Epdm Rubber Insulation Material, Aluminum Conductor Material, Black Insulation Color, 2 Conductors, -45 °C Operating Temperature, +90 °C Operating Temperature, 8.83 In Overall Length, Screw Terminal, 600 V Ac, 0.62 LB/Ea
Weight per unit	
Product Category	
Features	
Number of Conductors	2
Poles	1
Voltage Rating	600 V
Warranty	
Wire Size	2FO MCNA 12 AVA/C
Wire Type	Class B & C
Material, Color, and Finish	
Color	Black
Finish	EPDM Rubber Insulated
Housing Material	Aluminum
Dimensions and Weight	I 1 25 W 0 02 II 2 20
Size	L=1.25 - W=8.83 - H=3.38
Descriptions	
Description	12AWG-350MCM CONN
extra long description	NSI ISPBS350 POLARIS EDGE Connector
Features	The Polaris ISPBS350 2-Port In-Line Entry Submersible Connector
	provides the simplest solution for forming a secure connection between two conductors in direct burial or temporary submersal
	applications with a wide range of wire sizes. Sized for 350 MCM -
	12 AWG wires and rated for 600V, this pre-insulated connector comes pre-loaded with an oxide inhibitor and installs faster than traditional connector options using just a hex key and torque wrench. The aluminum alloy body is wrapped in high-dielectric str
Manufacturer Information	
OTINI	00443201707030

GTIN	00662381787828
UPC	662381787828



Elliott Electric Supply

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr. 75964-0000, TX Nacogdoches Phone: 936-569-7941 Fax: 936-560-4685

Ta	axonomi	ies, Cla	assificatio	ns, and C	ategories
		_			_

Category Description	Comp & Mech Lugs and Butt Splices
Type	Submersible Pedestal Connectors

Packaging

okaging	
Carton	3
Weight Per each	0.62

Uses, Certifications, and Standards

Application	Wire Termination
environmental conditions	90 C
standard	ANSI C119.4, C119.1, UL486D