



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2450 NE Inner Loop Building 1  
78626-0000, TX Georgetown  
Phone: 737-444-2615  
Fax: 737-444-2617



## JDL400 Low Peak Class J TD Fuse

*Edison Fuses*

Catalog Number	JDL400
Manufacturer	Edison Fuses
Description	Eaton Edison Series JDL Fuse, Time-Delay Current-Limiting Fuse, Non-Indicating, 400 A, Class J, 200 Kaic, Standard, 1, 600 V
Weight per unit	1.6 (lbs/each)
Product Category	Dual Element

### Features

amperage rating	400
dimensions	7.1300 IN X 2.1300 IN X 2.1300 IN
Fuse Class	Class J
interrupt rating	200 kAIC
Voltage Rating	600 V

### Descriptions

extra long description	EFSE JDL400 UL CLASS J TIME DELAY 6
Features	Edison's UL Class J fuse products are offered in both Dual-Element Time-Delay (JDL) and Fast-Acting (JFL) types. Both types have 200,000 amp interrupting rating at 600Vac RMS Sym amps. Their small physical size and high performance characteristics makes Class J fuses ideal for any space-limited applications. Edison's JFL fuses are best suited for the protection of non-inductive loads such as resistive heating and lighting circuits.
Long Description	Eaton Edison series JDL fuse, Time-delay current-limiting fuse, Non-indicating, 400 A, Class J, 200 kAIC, Standard, 1, 600 V
Product Type	UI Class J Time Delay 600
Special Features	Non-Indicating

### Manufacturer Information

Brand	Eaton
GTIN	00782634803591
Manufacturers Part Number	JDL400
UPC	782634803591

### Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	FUSE

### Availability

Status	Inactive
--------	----------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2450 NE Inner Loop Building 1  
78626-0000, TX Georgetown  
Phone: 737-444-2615  
Fax: 737-444-2617

## Packaging

Carton	1
Weight Per each	1.55

## Uses, Certifications, and Standards

Application	Datacenters - Facilities: Critical Power
standard	CSA Certified,UL Listed,CE Marked,RoHS Compliant