



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

706 Solon Rd.  
75165-0000, TX Waxahachie  
Phone: 972-937-6965  
Fax: 972-937-6968



## HBL2723 LKG Conn, 30A 3P 250V, L15-30R, B/W *Hubbell Wiring Devices*

Catalog Number	HBL2723
Manufacturer	Hubbell Wiring Devices
Description	Locking Devices, Twist-Lock®, Industrial, Female Connector Body, 30A 3-Phase Delta 250V Ac, 3-Pole 4-Wire Grounding, L15-30R, Screw Terminal, Black and White.
Weight per unit	0.4000 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

### Features

amperage rating	30
connection	Pressure Screw Terminal
Current Rating	30
insulation	Insulated Body
Material	Nylon
Number of Conductors	4
pallet quantity	3060
Poles	3-Pole
Voltage Rating	3 Phase 250

### Material, Color, and Finish

Color	Black;White
-------	-------------

### Dimensions and Weight

Size	2.33 in x 2.33 in x 3.86 in
------	-----------------------------

### Descriptions

Description	LKG CONN, 30A 3P 250V, L15-30R, B/W
extra long description	HWDK HBL2723 LKG CONN, 30A 3P 250V,
Long Description	Locking Devices, Twist-Lock®, Industrial, Female Connector Body, 30A 3-Phase Delta 250V AC, 3-Pole 4-Wire Grounding, L15-30R, Screw Terminal, Black and White.
Product Type	LKG Conn, 30A 3P 250V, L15-30R, B/W
Special Features	Standard Product

### Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585039251
Manufacturers Part Number	HBL2723
UPC	783585039251

### Taxonomies, Classifications, and Categories

Category Description	NEMA RATED TURNLOK PLUGS, CONNECTORS, & RECEPTICLES
Type	Connector Body



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

706 Solon Rd.  
75165-0000, TX Waxahachie  
Phone: 972-937-6965  
Fax: 972-937-6968

## Packaging

Carton	1
Package	30
Weight Per each	0.4

## Uses, Certifications, and Standards

Application	Heavy Duty Industrial
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Cord
nema rating	L15-30R
standard	Certified to CSA C22.2 No.42;Fed.Spec. W-C-596;Listed to UL 498