



FEATURES

- · T8 optimized fluorescent lensed troffer
- Shallow design frees up plenum space
- Hemmed fixture edges reduce risk of injury during fixture handling and installation
- Integral T-bar clips quickly secure fixture to the grid
- Corner hinging for easy insertion and removal of shielding frame
- Housing embossments provide extra strength and rigidity
- Housing ends secured by unique corner interlock and screws
- Snap-in ballast cover requires no tools for wireway access
- Flush steel shielding frame, screw assembled for easy diffuser replacement
- Rotary action cam latches. Smooth operating for secure shielding retention
- Metal to metal light leak protection on all four sides of shielding frame
- Rotary lock lampholders for positive lamp contact
- Heat sink embossments behind ballasts for cooler operation,
- Recessed, surface or cable mount
- UL listed 1598

PROJECT INFORMATION Project Name Type Catalog No. Date

CONSTRUCTION

Housing is constructed of heavy gauge steel, die formed for extra rigidity. Four T-bar clips integral to housing. Housing features hemmed edges. Door frame hinges and latches from either side. Wireway accessible from below for upgrades or maintenance.

BALLASTS

Energy efficient, thermally protected, automatic resetting, Class "P", high power factor, sound rated A, unless otherwise specified. For a specific vendor and/or ballast, specify as option. CEE NEMA Premium compliant.

ELECTRICAL

Standard class "P," thermally protected, auto resetting HPF ballast, sound rated A. CEE NEMA Premium compliant. All ballast leads extend a minimum of 6" through access location. NEC/CEC compliant ballast disconnect is standard.

All metal parts processed with a phase phosphate bonding treatment. Grid units are pre-painted with high gloss baked white enamel, 86% reflective. Polyester powder coat paint after fabrication (PAF) option available, reflectance 90%.

SHIELDING

100% virgin acrylic prismatic 12, extruded and roll-embossed, diagonally oriented female prisms standard. Other shielding may be specified. If desired shielding media is not shown in ordering guide, contact your local Hubbell Lighting representative.

CEILING COMPATIBILITY


Designed for recessed installation in standard inverted tee grid ceilings (G), recessed installation in hard ceilings (G with FK accessory), Surface mount at ceiling plane (SM) or cable mount suspension below ceiling plane (CM). For compatibility with specific ceilings contact your Hubbell Lighting representative.

CERTIFICATION

All luminaires are built to UL 1598 standards and bear appropriate UL and cUL or CSA labels. Damp location labeling is standard. Emergency-equipped fixtures labeled UL 924. UI Sanitation Approved.

ORDERING INFORMATION

EXAMPLE JT824-432G-FSA12-EU-F0735-C488-GLR



¹ For drywall order flange kit accessories separately

FK24 $2' \times 4'$ Flange Kit

FKCR Flange Kit Continuous Row Connector

CM48Y2SC3F-KIT 48" Cable Mount Kit for 2' wide CM ceiling

type, 3 Wire Feed Cord

Accessories.

Page 1/2 Rev. 05/21/19 LENSED TROFFERS / IT824-4



² Order hanger accessories separately.

³ Provides ends with wiring access for continuous row mounting.

ACCESSORIES (ORDER SEPARATELY)



PHOTOMETRIC DATA

LUMINAIRE DATA

Luminaire	JT824-432G-FSA12					
	J Lensed Troffer					
	2'x4' 4-Lamp with A-12 Pattern Acrylic Prismatic Lens					
Ballast	B432I120RH-A					
Ballast Factor	0.88					
Lamp	F32T8					
Lumens per Lamp	2950					
Watts	111					
Shielding Angle	N/A					
Spacing Criterion	0° = 1.22 90° = 1.32					


ZONAL LUMEN SUMMARY

Zone	Lumens	%Lamp	%Fixt.
0-30	3103	26.3	32.0
0-40	5053	42.8	52.0
0-60	8240	69.8	84.9
0-90	9707	82.3	100.0
0-180	9707	82.3	100.0

Test **I52515** Test Date **1/8/03**

ENERGY DATA								
Total Luminaire Efficiency	82.3%							
Luminaire Efficacy Rating (LER)	78							
ANSI/IESNA RP-1-2004 Compliance	Noncompliant							
Comparative Yearly Lighting Energy Cost per 1000 Lumens	\$3.08 based on 3000 hrs. and \$0.08 per KWH							

INDOOR CANDELA PLOT



AVG. LUMINANCE (Candela/Sq. M.)

	0.0	22.5	45.0	67.5	90.0
0	6159	6159	6159	6159	6159
30	5845	5961	6147	6335	6371
40	5293	5422	5641	5994	6082
45	4779	5007	5267	5608	5643
50	4307	4514	4765	5072	5079
55	3838	3944	4108	4370	4450
60	3365	3306	3274	3594	3766
65	3010	2769	2439	2940	3247
70	2973	2593	2098	2671	3101
75	3208	2706	2385	2803	3305
80	3356	3004	2842	3158	3564
85	3433	3577	3326	3829	3721
	30 40 45 50 55 60 65 70 75 80	0 6159 30 5845 40 5293 45 4779 50 4307 55 3838 60 3365 65 3010 70 2973 75 3208 80 3356	0 6159 6159 30 5845 5961 40 5293 5422 45 4779 5007 50 4307 4514 55 3838 3944 60 3365 3306 65 3010 2769 70 2973 2593 75 3208 2706 80 3356 3004	0 6159 6159 6159 30 5845 5961 6147 40 5293 5422 5641 45 4779 5007 5267 50 4307 4514 4765 55 3838 3944 4108 60 3365 3306 3274 65 3010 2769 2439 70 2973 2593 2098 75 3208 2706 2385 80 3356 3004 2842	0 6159 6159 6159 6159 30 5845 5961 6147 6335 40 5293 5422 5641 5994 50 4307 4514 4765 5072 55 3838 3944 4108 4370 60 3365 3306 3274 3594 65 3010 2769 2439 2940 70 2973 2593 2098 2671 75 3208 2706 2385 2803 80 3356 3004 2842 3158

COEFFICIENTS OF UTILIZATION (%)


	RC 80					70				50			0
	RW	70	50	30	10	70	50	30	10	50	30	10	0
RCR	1	90	86	83	80	88	85	82	79	81	79	76	70
	2	83	76	71	67	81	75	70	66	72	68	64	60
	3	76	68	61	56	74	66	61	56	64	59	55	51
	4	70	61	54	49	68	60	53	48	57	52	48	45
	5	65	55	48	42	63	54	47	42	52	46	42	39
	6	60	49	42	37	58	49	42	37	47	41	37	35
	7	56	45	38	33	54	44	38	33	43	37	33	31
	8	52	41	34	30	51	41	34	30	40	34	30	28
	9	49	38	31	27	47	37	31	27	36	31	27	25
	10	46	35	29	24	45	35	29	24	34	28	24	23

RCR = Room Cavity Ratio

 $\mathbf{RC} = \mathbf{Effective}$ Ceiling Cavity Reflectance $\mathbf{RW} = \mathbf{Wall}$ Reflectance


0.0 ——— 45.0 ———— 90.0 ———

DIMENSIONAL DATA




NOTE: All dimensions are in inches; dimensions and specifications are subject to change without notice. Please consult factory or check sample for verification.


CEILING COMPATIBILITY



For lay-in installation in exposed grid ceilings. Maximum tee widths of 1" and maximum tee heights of 2" allowed.



For hard ceiling applications order FK24 flange kit. Flange kit wires directly into concealed ceiling opening for a clean, finished appearance.



For flanged fixtures in row configurations, the FKCR adapter bracket kit is required in addition to the FK24 kit. Order one less FKCR than the total number of fixtures in row. (Example: Row of two, order (2) FK24 & (1) FKCR)


Row cut out dimensions using FK24 & FKCR adapters:

Width 24%", Length [48" \times (# in row)] + %". Example: (48" \times 2) + %"= 96%" Flange kit rough in dimensions for single unit only: 24%" \times 48%"

LENSED TROFFERS / JT824-4



DIMENSIONAL DATA - SURFACE MOUNT (SM) OR CABLE MOUNT (CM)



SURFACE MOUNT

Order SM ceiling type. Mounting collar required for surface mounting. (4) Mounting knock-outs, $\frac{1}{4}$ " to $\frac{1}{2}$ " provided as shown, marked "A".

CABLE MOUNT

Order CM ceiling type. Access plate supplied for cable mounting or suspension. Use CM48Y2SC3F-KIT 48" cable mount kit. Includes 3 wire feed cord. For other wiring needs, contact Hubbell Lighting representative. Mounting knock-outs, ¼" to ½", provided as shown, marked "A".

Page 3/2 Rev. 05/21/19 LENSED TROFFERS / JT824-4

