



KS39, Split Bolt Connector, Run/Tap: 4/0 AWG Str-750 kcmil

By Burndy
Catalog # [KS39](#)

Copper Split Bolt, Cu: 4/0 AWG (Str)-750 kcmil (Run & Tap).



Application

For Direct Burial Cables

General

Connector Type	Split Bolt
EU RoHS Indicator	Yes
Installation Torque Recommended in-lb	1000 in
Material	Copper
Plated	N
Plating Type	Unplated
Sub Brand	SERVIT
Trade Name	SERVIT®
Type	KS
UPC	781810014752
UPC 12 Digit	7818100147522

Dimensions

Dimension - B Length inch	1.75 in
Dimension - Cross Flats inch	2.31 in
Dimension - L Length Overall mm	84 mm
Dimension - Length Overall inch	3.51
Dimension - Width inch	1.94 in
Dimension - Width mm	49 mm
Width	1.94 in

Conductor Related

Conductor - Copper Str Run	4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil
Conductor - Copper Str Run Range	4/0 STR - 750 KCMIL
Conductor - Copper Str Tap	4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil
Conductor - Copper Str Tap Range	4/0 STR - 750 KCMIL
Conductor - CopperWeld Str Run	19 #5
Conductor - CopperWeld Str Run Range	19 #5
Conductor - CopperWeld Str Tap	19 #5
Conductor - CopperWeld Str Tap Range	19 #5
Conductor Type	<ul style="list-style-type: none">• CU C Str-Run• CU Weld C Str-Run• CU C Str-Tap• CU Weld C Str-Tap

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none">• UL 486A• UL486B
Standards - Industry Standards Met	<ul style="list-style-type: none">• UL 486A• UL486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

3D Models - KS39_MODEL-PDF
3D Models - KS39_MODEL-STEP
3D Models - KS39_MODEL-IGES
Catalogs - Full Line BURNDY Catalog
Customer Notices - Prop 65 Notice
Sales Drawings - SD..078561-01



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-KS39-SPEC-EN | REV 8/2023