



KS39

by Burndy
Catalog ID: KS39

Prop 65 Notice

Copper Split Bolt, Cu: 4/0 AWG (Str)-750 kcmil (Run & Tap).

Features: Compact, High Strength, High Copper Alloy SERVIT Split-Bolt Has Free-Running Threads And Easy To Grip Wrench Flats, Highly Resistant To Season Cracking And Corrosion, The SERVIT Provides Maximum Pressure And Assures A Secure Connection On All Combinations Of Run And Tap Conductors, Installation Torque: 1000 IN-LB, Conductor Type: Run: Commercial Stranded And Solid Copper, Stranded Copperweld, Tap: Commercial Stranded And Solid Copper, Stranded Copperweld, Length: 3.29 IN, Width: 1.94 IN, Cross Flats: 2.31 IN

Product Details

General

Application	For Direct Burial Cables
Connector Type	Split Bolt
Installation Torque Recommended in-lb	1000 in
Material	Copper
Plated	N
Plating Type	Unplated
Sub Brand	SERVIT
Trade Name	SERVIT®
Type	KS
UPC	781810014752
UPC 12 Digit	7818100147522

Dimensions

Dimension - B Length inch	1.75 in
Dimension - Cross Flats inch	2.31 in
Dimension - L Length Overall mm	84 mm
Dimension - Length Overall inch	3.51
Dimension - Width inch	1.94 in
Dimension - Width mm	49 mm
Width	1.94 in

Conductor Related

Conductor - Copper Str Run	4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil
Conductor - Copper Str Run Range	4/0 STR - 750 KCMIL
Conductor - Copper Str Tap	4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil
Conductor - Copper Str Tap Range	4/0 STR - 750 KCMIL
Conductor - CopperWeld Str Run	19 #5
Conductor - CopperWeld Str Run Range	19 #5

Conductor - CopperWeld Str Tap	19 #5
Conductor - CopperWeld Str Tap Range	19 #5
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Run • CU Weld C Str-Run • CU C Str-Tap • CU Weld C Str-Tap

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> • UL 486A • UL486B
Standards - Industry Standards Met	<ul style="list-style-type: none"> • UL 486A • UL486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)