



# KS44, Split Bolt Connector, Run/Tap: 300-1000 kcmil

By Burndy  
Catalog # [KS44](#)



Copper Split Bolt, Cu: 300-1000 kcmil (Run & Tap).

## Application

For Direct Burial Cables

## General

|                                       |               |
|---------------------------------------|---------------|
| Connector Type                        | Split Bolt    |
| EU RoHS Indicator                     | Yes           |
| Installation Torque Recommended in-lb | 1100 in       |
| Material                              | Copper        |
| Plated                                | N             |
| Plating Type                          | Unplated      |
| Sub Brand                             | SERVIT        |
| Trade Name                            | SERVIT®       |
| Type                                  | KS            |
| UPC                                   | 781810015001  |
| UPC 12 Digit                          | 7818100150011 |

## Dimensions

|                                 |         |
|---------------------------------|---------|
| Dimension - B Length inch       | 2.10 in |
| Dimension - Cross Flats inch    | 2.56 in |
| Dimension - L Length Overall mm | 95 mm   |
| Dimension - Length Overall inch | 3.9     |
| Dimension - Width inch          | 2.19 in |
| Dimension - Width mm            | 56 mm   |
| Width                           | 2.19 in |

## Conductor Related

|                                  |  |
|----------------------------------|--|
| Conductor - Copper Str Run       | 300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil;800 kcmil;850 kcmil;900 kcmil;1000 kcmil   |
| Conductor - Copper Str Run Range | 300 KCMIL - 1000 KCMIL   |
| Conductor - Copper Str Tap       | 4/O AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil;800 kcmil;850 kcmil;900 kcmil;1000 kcmil   |
| Conductor - Copper Str Tap Range | 300 KCMIL - 1000 KCMIL   |
| Conductor Type                   | <ul style="list-style-type: none"> <li>• CU C Solid-Run</li> <li>• CU C Str-Run</li> <li>• CU Weld C Solid-Run</li> <li>• CU Weld C Str-Run</li> <li>• CU C Str-Tap</li> <li>• CU Weld C Solid-Tap</li> <li>• CU Weld C Str-Tap</li> <li>• CU C Solid-Tap</li> </ul> |

## Certifications and Compliance

|   |   |
|---|---|
| Certification - CSA Approved            | No  |
| Certification - ETL                     | No  |
| Certification - UL Listed Direct Burial | Yes   |
| Certification - UL Recognized           | No  |
| Certification - cULus                   | No  |
| Industry Standard(s)                    | <ul style="list-style-type: none"> <li>• UL 486A</li> <li>• UL486B</li> </ul> |
| Standards - Industry Standards Met      | <ul style="list-style-type: none"> <li>• UL 486A</li> <li>• UL486B</li> </ul> |
| Standards - RoHS Compliance Status      | EX  |
| UL Listed                               | Yes   |

## Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

## Product Assets

[3D Models - KS44\\_MODEL-IGES](#)  
[3D Models - KS44\\_MODEL-PDF](#)  
[3D Models - KS44\\_MODEL-STEP](#)  
[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - SD..078561-01](#)



**A proud member of the Hubbell Family.**

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-KS44-SPEC-EN | REV 8/2023