



UPC: 192552026932



Color: Clear



Weight: 0.0 lbs

Project:	Type:
Prepared By:	Date:

Technical Specifications

Performance

Description:

Field adjustable lumen output and CCT provide installation flexibility when replacing traditional HID. Integrated AUX port to add lamp-level sensor control.

Wattage Equivalency:

75W/125W/150W Metal Halide

Input Wattage:

18W/27W/36W

Lumens (Nominal):

18W:
3000K @ 2,430 Lm; 4000K @ 2,610 Lm; 5000K @ 2,520 Lm
27W:
3000K @ 3,645 Lm; 4000K @ 3,915 Lm; 5000K @ 3,780 Lm
36W:
3000K @ 4,860 Lm; 4000K @ 5,220 Lm; 5000K @ 5,040 Lm

Efficacy:

18W/27W/36W:
3000K @ 135 Lm/W; 4000K @ 145 Lm/W; 5000K @ 140 Lm/W

L70 Lifespan:

50,000-Hour LED lifespan based on IES LM-70 results

Electrical

Dimmable:

Yes via the Lightcloud Blue mobile app and devices. This lamp will not operate properly when connected to a standard (incandescent) dimmer or dimming control.

Input Voltage:

100-277V

Operating Frequency:

50/60Hz

Input Current @ 120V (mA):

309 mA

Input Current @ 208V (mA):

184 mA

Input Current @ 240V (mA):

163 mA

Input Current @ 277V (mA):

133 mA

Operating Temperature:

-22°F to 140°F (-30°C to 60°C)

Flicker:

<30%

Surge Protection:

4kV

LED Characteristics

R9 Value:

High color performance with R9 no less than 0

Color Consistency:

<6-step MacAdam Ellipse binning to achieve consistent fixture-to-fixture color

Color Stability:

LED color temperature is warranted to shift no more than 200K in color temperature over a 5-year period

Color Uniformity:

RAB's range of Correlated Color Temperature follows the guidelines of the American National Standard for Specifications for the Chromaticity of Solid State Lighting (SSL) Products, ANSI C78.377-2017.

Installation

Installation Method:

UL Type B, Ballast Bypass

Installation Orientation:

Vertical and Horizontal

Construction

Base Type:

E26 Edison

Finish:

Clear

Bulb Shape:

Post top (sensor)

HIDFA-36S-E26-8CCT-BYP/5SP

**THD:**

≤20%

Power Factor:

≥0.9

Color Temperature:

Field adjustable via dip switch 3000K/4000K/5000K

Color Accuracy (CRI):

≥80 CRI

Endcap Material:

Metal

Technical Specifications (continued)

Enclosure Material:

Polycarbonate

Compliance

Safety Listing:

UL Listed, UL Classified

Environment:

Suitable for use in dry and damp environments

Fixture Rating:

Suitable for use in enclosed fixtures

IP Rating:

IP64

California Energy Commission (CEC) Status:

Lawful for Sales in California

RoHS:

Mercury and UV free. RoHS-compliant components.

FCC:

Complies with Part 15B of the FCC Rules

Other

Compatible Products:

Add the Lightcloud Blue 5-Pin Plug-in Controller with optional sensor to connect to the Lightcloud Blue Bluetooth Mesh Wireless Network Lighting Control System. Learn more about Lightcloud Blue.

Accessories:

CONTROL/W/AUX/5SP/LCB

Lightcloud Blue 5-Pin Plug-in Controller

CONTROL/W/AUX/5SP/LCBS

Lightcloud Blue 5-Pin Plug-in Controller with PIR Sensor

CONTROL/W/AUX/5SP/LCBS/MVS

Lightcloud Blue 5-Pin Plug-in Controller with MVS Sensor

Warranty:

RAB warrants that our LED products will be free from defects in materials and workmanship for a period of five (5) years from the date of delivery to the end user, including coverage of light output, color stability, driver performance and fixture finish. RAB's warranty is subject to all terms and conditions found at rablighting.com/warranty.

Note:

All values are typical (tolerance +/- 10%)


Buy American Act Compliance:

RAB values USA manufacturing! Upon request, RAB may be able to manufacture this product to be compliant with the Buy American Act (BAA). Please contact customer service to request a quote for the product to be made BAA compliant.

Case and Pallet Dimensions

	QTY	LENGTH (in)	WIDTH (in)	HEIGHT (in)
CASE	12	15.55	11.61	10.39
PALLET	17	48	40	41.04

Dimension



Features

- Replaces traditional metal halide or high pressure sodium HID lamp
- Adjustable wattage and CCT allows for in-field customization
- Integral driver enables lamp to be wired directly to line voltage without need for an external driver or ballast
- Rated for use in enclosed fixtures in dry or damp locations

Ordering Matrix

Family	Wattage	Base Type	CRI/Color Temp	Installation Type	Sensor
HIDFA	36S	E26	8CCT	BYP	/5SP
	27S = 27/18/12W 36S = 36/27/18W 45S = 45/36/27W 54S = 54/45/36W 63S = 63/54/45W 80S = 89/63/54W 100S = 100/80/63W 120S = 120/100/80W	EX39 = EX39 Extended Mogul E26 = E26 Edison	8CCT = 80 CRI, CCT Selectable	BYP = Ballast Bypass	Blank = No Sensor /3SP = 3-Pin Sensor Port /5SP = 5-Pin Sensor Port