



# KT-LED14.5T8-48G-850-DX2

#### **DESCRIPTION**

14.5W T8 LED | 5000K | >83 CRI | High-Efficiency | Single- or Double-ended Wiring
















#### **PRODUCT FEATURES**

- Replacement for conventional fluorescent lamp
- Single- or double-ended wiring
- 50,000+ hour lifetime
- Approximately 40% more energy efficient than standard F32T8 lamps
- Environmentally friendly: No mercury used
- Instant startup

- Frosted lens eliminates pixelation
- UL classified
- Operating temperature: -20°C/-4°F to 45°C/113°F
- Integral driver (isolated) eliminates the need for external driver or ballast
- 110+ Lumens per Watt

#### **OPERATING SPECIFICATIONS**

# **ELECTRICAL CHARACTERISTICS**

Input Voltage	Power Consumption	Power Factor	Input Current
120-277Vac	14.5W	>0.9	0.15A @ 120V 0.06A @ 277V


# PHOTOMETRIC CHARACTERISTICS

Color Temperature (CCT)	5000K	
Luminous Flux	1890 lm	
Color Rendering Index (CRI)	>83	
Efficacy	130 lm/W	
Beam Angle	240°	
Visible Light Area	325°	


### **RATED LIFE**

L70 (Hours)	50,000

# SPECTRAL DISTRIBUTION



# POLAR CANDELA DISTRIBUTION



Maximum Candela = 1248.55 Located at

Horizontal Angle=0, Vertical Angle=0

- 1 Violet Vertical Plane through Horizontal Angles (90–270)
- 2 Green Vertical Plane through Horizontal Angles (0–180)







# KT-LED14.5T8-48G-850-DX2

#### SINGLE-ENDED WIRING DIAGRAM


1. Cut all existing connections to ballast as shown below and remove ballast. See *Figure A* for typical ballast configurations. **Note: Single-ended wiring requires non-shunted lampholders.** 



2. Rewire figure as shown below.



# TYPICAL NON-SHUNTED LAMPHOLDER



Connect wires directly to these terminals


# CAUTION: FOR SINGLE-ENDED WIRING USE ONLY NON-SHUNTED LAMPHOLDERS.

For Single-ended wiring, do not install product in a fixture with shunted lampholders (found in all fixtures using instant start ballasts). If the current lampholders are shunted, remove them and replace them with non-shunted lampholders. Make new connections directly to terminals as indicated above. Keystone can provide any style replacement lampholders. Call us at 800-464-2680.

# **DOUBLE-ENDED WIRING DIAGRAM**

- 1. Cut all existing connections to ballast as shown below and remove ballast. See Figure A above for typical ballast configurations.
- 2. Re-wire fixture as shown below. For double-ended wiring, use either shunted or nonshunted lampholders.

NOTE: There should not be any exposed wires at the end of installation.








# KT-LED14.5T8-48G-850-DX2 T8 LED LAMP

#### PHYSICAL CHARACTERISTICS



#### LAMP DIMENSIONS

A (Body Length)	47.15"	
B (Illuminated Length)	42.63"	
C (Diameter)	1.10"	

**NOMINAL LENGTH: 48**"

BASE TYPE: G13 (Medium Bi-Pin)

#### ORDERING INFORMATION

ORDER CODE	PACKAGING STYLE	PACK QTY.	ITEM STATUS
KT-LED14.5T8-48G-850-DX2-CP	Carton Pack (Egg Crate Packaging)	25	Quick Ship

# **CATALOG NUMBER BREAKDOWN**

KT-LED14.5T8-48G-850-DX2-CP

- 1 Keystone Technologies
- 2 LED Lamp
- 3 Wattage
- 4 Lamp Type
- 5 Nominal Length (Inches)
- **6** Glass Construction
- **7** 800 Series
- **8** Color Temperature
- 9 Single- or Double-Ended Wiring
- 10 Packaging Style