

ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1800 S. May Ave. 73108-0000, OK Oklahoma City Phone: 405-896-3723 Fax: 405-272-3057

HS12 3/16" High Speed Steel Drill L.H. Dottie CO.

Catalog Number	HS12
Manufacturer	L.H. Dottie CO.
Description	High Speed Drill, M2 Grade, Steel Material, Black/Gold Finish, Split Point Type, 135 Deg Split Drill Point, 3/16 In. Fractional Size, 3-1/2 In. Overall Length, 3/16 In. Shank Diameter
Weight per unit	0.0070 (lbs/each)
Product Category	Bits, Parts, Accessories

Features

Grade	M2	
Material	High Speed Steel	
Number of Pieces	3	
Point Type	Split Point	
Shank Diameter	3/16	

Material, Color, and Finish

F	nish	Black/Gold

Dimensions and Weight

Overall	Length	3-1	1/	2	١
Overall	Lengin	 ა-	1/	_	

Descriptions

Description	3/16" HIGH SPEED STEEL DRILL
extra long description	DOTTIE HS12 3/16" High Speed Steel
Long Description	High Speed Drill, M2 grade, Steel material, Black/Gold finish, Split
	Point Type, 135 DEG Split drill point, 3/16 in. fractional size, 3-1/2
	in. overall length, 3/16 in. shank diameter
Product Type	3/16" High Speed Steel Drills
Special Features	Features: Industrial Quality, Heavy Duty Jobber Length, Fractional
	Sizes

Manufacturer Information

Brand	L.H. Dottie CO.	
GTIN	00781002293125	
Manufacturers Part Number	HS12	
UPC	781002293125	

Taxonomies, Classifications, and Categories

Category Description	TOOL BAG/POUCHES
Туре	High Speed Drill

Packaging

Carton	12
Weight Per each	0.007

1800 S. May Ave. 73108-0000, OK Oklahoma City Phone: 405-896-3723 Fax: 405-272-3057

U	lses, (Certifi	ications	, and $\mathfrak S$	Stand	lard	S

Application	For Steel, Steel Forging, Cast Iron and Other Work M	/laterials
-------------	--	------------