

TECHNICAL DATA SHEET - INTERACTIVE PDF

Cable Tie, standard, 120lb series

Natural and UV resistant black

Catamount*



Ratings:

• Tensile Strength: 120lbs (534N)

• Min. Operating Temperature: -40°F (-40°C)

• Max. Operating Temperature: 185°F (85°C)

• Min. Installation Temperature: -4°F (-20°C)

Installation:

 Install with approved ABB cable tie tool such as ERG120

Materials / Finishes:

- Natural Polyamide (Nylon 6.6)
- UV-resistant black (Nylon 6.6)

Conforms to:

- AH-2 Plenum Rated
- UL94 V-2

Cable ties are primarily used to cinch wires and cables together to form a neat and organized bundle.


Certifications / Standards:







3-Part Specification: End User Tools



Product selection - in. (mm)							
Part no:	A ±0.25 (6.4)	B ±0.02 (0.5)	±0.06 (1.5)	D ±0.06 (1.5)	±0.02 (0.5)	Min. bundle dia.	Max. bundle dia.
L-14-120-0-C UV resistant	15.0 (381)	0.3 (7.7)	0.30 (7.6)	0.49 (12.5)	0.07 (1.8)	0.19 (4.8)	4.0 (101.6)
L-14-120-0-L UV resistant							
L-14-120-9-C Natural							
L-14-120-9-L Natural							

Note: Product must be installed in accordance with applicable national and local electrical codes.

tnb.abb.com (US/Latin America) tnb.ca.abb.com (Canada) abb.com