


TECHNICAL DATA SHEET - INTERACTIVE PDF

Cable Tie, standard, 50 lbs. series

Natural and UV resistant black

Catamount®



Ratings:

- Tensile Strength: 50lb (222N)
- Min. Operating Temperature: -40°F (-40°C)
- Max. Operating Temperature: 185°F (85°C)
- Min. Installation Temperature: -4°F (-20°C)

Installation:

- Install with approved ABB cable tie tool such as ERG50, QC-100, L-200, L-400-C

Materials / Finishes:

- Natural Polyamide (Nylon 6.6)
- UV-resistant black (Nylon 6.6)

Conforms to:

- AH-2 Plenum Rated
- UL94 V-2
- Type 21S

Cable ties are primarily used to cinch wires and cables together to form a neat and organized bundle.

Certifications / Standards:



3-Part Specification: End User Tools

Product selection - in. (mm)							
Part no: GID no:	A	B	C	D	E	Min. bundle dia.	Max. bundle dia.
L-7-50-0-C 7TAG054290R0012	±0.25 (6.4)	±0.01 (0.25)	±0.03 (0.76)	±0.03 (0.76)	±0.01 (0.25)	0.06 (1.57)	1.87 (47.6)
L-7-50-0-M 7TAG054330R0007							
L-7-50-9-C 7TAG054290R0013							
L-7-50-9-M 7TAG054330R0008							
L-11-50-0-C 7TAG054290R0006	11.1 (282)	0.18 (4.6)	0.20 (5.1)	0.30 (7.6)	0.06 (1.5)	0.06 (1.57)	3.0 (76.2)
L-11-50-0-D 7TAG054330R0004							
L-11-50-9-C 7TAG054290R0007							
L-11-50-9-D 7TAG054330R0005							
L-14-50-0-C 7TAG054290R0008	14.6 (371)	0.18 (4.6)	0.20 (5.1)	0.30 (7.6)	0.06 (1.5)	0.06 (1.57)	4.00 (101.6)
L-14-50-9-L 7TAG054980R0607							
L-14-50-0-L 7TAG054310R0026							
L-14-50-0-D 7TAG054330R0006							
L-14-50-9-C 7TAG054290R0010							
L-14-50-9-D 7TAG054320R0002							

Note: Product must be installed in accordance with applicable national and local electrical codes.

-0 in part number = UV resistant black
-9 in part number = Natural