

## Insulating Bushings (Split Threaded Plastic)

Fittings



IBTS-400

Part Number	Size	Std. Pkg.
IBTS-50	1/2"	50
IBTS-75	3/4"	50
IBTS-100	1"	25
IBTS-125	1-1/4"	25
IBTS-150	1-1/2"	25
IBTS-200	2"	25
IBTS-250	2-1/2"	10
IBTS-300	3"	10
IBTS-350	3-1/2"	10
IBTS-400	4"	10
IBTS-500	5"	10
IBTS-600	6"	10

**Application:** These split, threaded insulating bushings are used on threaded rigid or IMC conduits when existing wires have already been pulled and an insulating bushing is required on the pipe.

**Advantages:** Garvin Industries' split, threaded insulating bushing design easily wraps around cables and screws on, ensuring a secure and tight fit. They can even be used with PVC cement to ensure the plastic remains glued together.

**Field Names:** Split insulating bushing, split wire protector bushing, split insulating bushing, split open insulating bushing, split insulator bushing, split rigid bushing, split a bushings.

**Material:** Plastic



IBTS-200 INSTALLATION

## Replace Old Industrial Fixtures!

Plate Mounts to Any Style Box  
& Provides Holes to Hang New  
Energy Efficient T5 Fixtures

- Attaches to any ceiling box or device ring
- No need to re-pipe to new location for adding fixture
- 1/2" knockout allows access to box through cover
- Use with chain and hooks or cable
- May be used in industrial or commercial applications
- Rugged steel construction



See Page 375 for more information!