PASS & SEYMOUR®

Isolated Ground Devices

Specification Grade IG 15 & 20A, 125V




Isolated ground receptacle with durable, solid construction.

IG5262, IG5362, TRIG5362 and TRIG5262

Featuring an impact-resistant nylon face, plated steel strap, and triple-wipe brass power contacts, these receptacles are built tough. They also feature our patented screw-pressure plate back wire clamp on ground for fast installation.

Features & Benefits



IG symbol and "Isolated Ground" markings for easy I.D. and circuit delineation

Triple-wipe brass contacts ensure lasting, positive contact with plug blades.

High-impact resistant nylon face resists impacts and scrapes.

Corrosion-resistant, plated steel strap

Patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.

Plastic barrier isolates grounding terminal from mounting strap and metal boxes.

Side and internal screw-pressure-plate back wire capability with #14 – #10 AWG copper or copper-clad, solid or stranded wire.

Auto-ground clip assures positive ground.

IG5262

Vertical Markets

- **Office**
- **Education**
- **Institutional**
- **Hospitality/Lodging**
- **Retail**


3rd Party Compliance

c UL us LISTED

UL Listed, File Number E140596, Standard UL498. Fed Spec WC596. CSA Certified File Number LR16063, Standard CSA-C22.2 No. 42 General Use Receptacles. Conforms to NEMA WD-1 and WD-6.

Technical Information

Performance	
Electrical	
Dielectric Withstand Voltage	Withstands 2000V minimum
Maximum Working Voltage	250V
Current Interrupting	Certified for current interrupting at full-rated current
Temperature Rise	Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current
Mechanical	
Terminal Identification	Terminal Identification in accordance with UL 498 (Brass, White, Green)
Terminal Accommodation	#14 AWG - #10 AWG copper conductor only
Product Identification	Ratings are permanent part of the device
Environmental	
Flammability	UL94 V2
Operating Temperature	Maximum continuous +60°C, minimum -40°C (without impact)



IG5262

Materials	
Face	Nylon
Back Body	PVC
Line Contacts	.032 688 Brass
Mounting Strap	.042" Plated Steel
Ground Contacts	.040" 260 Brass
Pressure Plate	.080" Steel
Terminal Screws	#8 Tri-Drive Steel
Ground Screw	#8 Hex Tri-Drive Steel
Assembly Drive Screw	Plated Steel
Auto-Ground Clip	Steel
Mounting Screws	Tri-Drive Steel
Ground Wire Pressure Plate	Brass
Tamper-Resistant Shutters	Thermoplastic (for TR models)

Warranty

1 Year

Ordering Information

Duplex Receptacles Back & Side Wire

Catalog Number	Ratings	Color	NEMA Config.
IG5262	15A 125V	Orange	5-15R
IG5262I	15A 125V	Ivory	5-15R
IG5262GRY	15A 125V	Gray	5-15R
IG5262RED	15A 125V	Red	5-15R
IG5262LA	15A 125V	Light Almond	5-15R
TRIG5262	15A 125V	Orange	5-15R
TRIG5262I	15A 125V	**Ivory**	5-15R
TRIG5262GRY	15A 125V	**Gray**	5-15R
TRIG5262LA	15A 125V	**Light Almond**	5-15R
TRIG5262BK	15A 125V	**Black**	5-15R
TRIG5262W	15A 125V	White	5-15R
IG5362	20A 125V	Orange	5-20R
IG5362I	20A 125V	Ivory	5-20R
IG5362W	20A 125V	White	5-20R
IG5362GRY	20A 125V	Gray	5-20R
IG5362RED	20A 125V	Red	5-20R
IG5362LA	20A 125V	Light Almond	5-20R
TRIG5362	20A 125V	Orange	5-20R
TRIG5362I	20A 125V	Ivory	5-20R
TRIG5362GRY	20A 125V	Gray	5-20R
TRIG5362RED	20A 125V	Red	5-20R
TRIG5362LA	20A 125V	Light Almond	5-20R
TRIG5362W	20A 125V	White	5-20R
TRIG5362BK	20A 125V	**Black**	5-20R



NEMA 5-15R



NEMA 5-20R

For more information on these and other P&S products refer to our Catalog or visit our web site.

Also available...

- **USB Charging Devices**
- **Hospital Grade Devices**
- **PlugTail® Wiring Devices**
- **Ground Continuity Monitoring (GCM)**
- **Straight Blade Plugs & Connectors**
- **Turnlok® Locking Devices**
- **SPD & Isolated Ground Devices**
- **IEC 309 Industrial Products**
- **Flexcor® Wire Mesh Grips**

The paper used to print this document is an environmentally responsible paper with 10% post consumer waste, with FSC and SFI Chain of Custody certifications, Lacey Act complaint. 100% of the electricity used to manufacture Flo sheets is generated with Green-e certified renewable energy.

All brand and product names referenced in this document are registered trademarks or trademarks of their respective holders.

Legrand, North America
60 Woodlawn Street
West Hartford, CT 06110
1.877.BY.LEGRAND (295.3472)
www.legrand.us

Canada
905.738.9195
www.legrand.ca

FOLLOW US

CS3356 — October 2024 **©2024 Legrand All Rights Reserved**

PASS & SEYMOUR®

Isolated Ground Devices

Specification Grade IG 15 & 20A, 125V




Isolated ground receptacle with durable, solid construction.

IG5262, IG5362, TRIG5362 and TRIG5262

Featuring an impact-resistant nylon face, plated steel strap, and triple-wipe brass power contacts, these receptacles are built tough. They also feature our patented screw-pressure plate back wire clamp on ground for fast installation.

Features & Benefits



IG symbol and "Isolated Ground" markings for easy I.D. and circuit delineation

Triple-wipe brass contacts ensure lasting, positive contact with plug blades.

High-impact resistant nylon face resists impacts and scrapes.

Corrosion-resistant, plated steel strap

Patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.

Plastic barrier isolates grounding terminal from mounting strap and metal boxes.

Side and internal screw-pressure-plate back wire capability with #14 – #10 AWG copper or copper-clad, solid or stranded wire.

Auto-ground clip assures positive ground.

IG5262

Vertical Markets

- **Office**
- **Education**
- **Institutional**
- **Hospitality/Lodging**
- **Retail**


3rd Party Compliance

c UL us LISTED

UL Listed, File Number E140596, Standard UL498. Fed Spec WC596. CSA Certified File Number LR16063, Standard CSA-C22.2 No. 42 General Use Receptacles. Conforms to NEMA WD-1 and WD-6.

Technical Information

Performance	
Electrical	
Dielectric Withstand Voltage	Withstands 2000V minimum
Maximum Working Voltage	250V
Current Interrupting	Certified for current interrupting at full-rated current
Temperature Rise	Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current
Mechanical	
Terminal Identification	Terminal Identification in accordance with UL 498 (Brass, White, Green)
Terminal Accommodation	#14 AWG - #10 AWG copper conductor only
Product Identification	Ratings are permanent part of the device
Environmental	
Flammability	UL94 V2
Operating Temperature	Maximum continuous +60°C, minimum -40°C (without impact)



IG5262

Materials	
Face	Nylon
Back Body	PVC
Line Contacts	.032 688 Brass
Mounting Strap	.042" Plated Steel
Ground Contacts	.040" 260 Brass
Pressure Plate	.080" Steel
Terminal Screws	#8 Tri-Drive Steel
Ground Screw	#8 Hex Tri-Drive Steel
Assembly Drive Screw	Plated Steel
Auto-Ground Clip	Steel
Mounting Screws	Tri-Drive Steel
Ground Wire Pressure Plate	Brass
Tamper-Resistant Shutters	Thermoplastic (for TR models)

Warranty

1 Year

Ordering Information

Duplex Receptacles Back & Side Wire

Catalog Number	Ratings	Color	NEMA Config.
IG5262	15A 125V	Orange	5-15R
IG5262I	15A 125V	Ivory	5-15R
IG5262GRY	15A 125V	Gray	5-15R
IG5262RED	15A 125V	Red	5-15R
IG5262LA	15A 125V	Light Almond	5-15R
TRIG5262	15A 125V	Orange	5-15R
TRIG5262I	15A 125V	**Ivory**	5-15R
TRIG5262GRY	15A 125V	**Gray**	5-15R
TRIG5262LA	15A 125V	**Light Almond**	5-15R
TRIG5262BK	15A 125V	**Black**	5-15R
TRIG5262W	15A 125V	White	5-15R
IG5362	20A 125V	Orange	5-20R
IG5362I	20A 125V	Ivory	5-20R
IG5362W	20A 125V	White	5-20R
IG5362GRY	20A 125V	Gray	5-20R
IG5362RED	20A 125V	Red	5-20R
IG5362LA	20A 125V	Light Almond	5-20R
TRIG5362	20A 125V	Orange	5-20R
TRIG5362I	20A 125V	Ivory	5-20R
TRIG5362GRY	20A 125V	Gray	5-20R
TRIG5362RED	20A 125V	Red	5-20R
TRIG5362LA	20A 125V	Light Almond	5-20R
TRIG5362W	20A 125V	White	5-20R
TRIG5362BK	20A 125V	**Black**	5-20R



NEMA 5-15R



NEMA 5-20R

For more information on these and other P&S products refer to our Catalog or visit our web site.

Also available...

- **USB Charging Devices**
- **Hospital Grade Devices**
- **PlugTail® Wiring Devices**
- **Ground Continuity Monitoring (GCM)**
- **Straight Blade Plugs & Connectors**
- **Turnlok® Locking Devices**
- **SPD & Isolated Ground Devices**
- **IEC 309 Industrial Products**
- **Flexcor® Wire Mesh Grips**

The paper used to print this document is an environmentally responsible paper with 10% post consumer waste, with FSC and SFI Chain of Custody certifications, Lacey Act complaint. 100% of the electricity used to manufacture Flo sheets is generated with Green-e certified renewable energy.

All brand and product names referenced in this document are registered trademarks or trademarks of their respective holders.

Legrand, North America
60 Woodlawn Street
West Hartford, CT 06110
1.877.BY.LEGRAND (295.3472)
www.legrand.us

Canada
905.738.9195
www.legrand.ca

FOLLOW US

CS3356 — October 2024 **©2024 Legrand All Rights Reserved**