



SPEC GRADE TURNLOK® LOCKING DEVICES, 30A SINGLE RECEPTACLE

L630R | [Pass & Seymour](#)

FEATURES & BENEFITS

Features high-quality, brass contacts for rock-solid electrical connections and long service life. Single-piece, solid brass or steel straps and impact-resistant nylon face and body help it shrug off hard use.



- Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.
- Face color coding by voltage facilitates locating and mating of proper devices.
- One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.
- Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.
- Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.
- Side and external screw-pressure-plate back wire capability.
- Accepts #14 - #10 AWG.

SPECIFICATIONS

GENERAL INFO

Type: Single Receptacles
Number Of Wires: 3

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Standard: Yes
CUL Listing No: No
cURus: No
Federal Spec: Yes
UL Listing No: 498
UL Standard: Yes
UN SPSC: 39121403
UR: No

DIMENSIONS

Depth (US): 1.28"

Height (US): 3.28"

Width (US): 1.61"

TECHNICAL INFORMATION

Amps: 30A

NEMA Configuration Number: L6-30R

Volts: 250V

Volts (AC): 250

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant





SPEC GRADE TURNLOK® LOCKING DEVICES, 30A SINGLE RECEPTACLE

L630R | [Pass & Seymour](#)

FEATURES & BENEFITS

Features high-quality, brass contacts for rock-solid electrical connections and long service life. Single-piece, solid brass or steel straps and impact-resistant nylon face and body help it shrug off hard use.



- Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.
- Face color coding by voltage facilitates locating and mating of proper devices.
- One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.
- Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.
- Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.
- Side and external screw-pressure-plate back wire capability.
- Accepts #14 - #10 AWG.

SPECIFICATIONS

GENERAL INFO

Type: Single Receptacles
Number Of Wires: 3

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Standard: Yes
CUL Listing No: No
cURus: No
Federal Spec: Yes
UL Listing No: 498
UL Standard: Yes
UN SPSC: 39121403
UR: No

DIMENSIONS

Depth (US): 1.28"

Height (US): 3.28"

Width (US): 1.61"

TECHNICAL INFORMATION

Amps: 30A

NEMA Configuration Number: L6-30R

Volts: 250V

Volts (AC): 250

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

