



KT-LED63HID-EX39-850-D /G3 HID REPLACEMENT LED LAMP

DESCRIPTION

63W HID Replacement LED Lamp | 5000K | > 80 CRI | IP64 Rated

LAMP TYPE: HID Replacement LED

BASE TYPE: EX39 (Mogul)

WATTAGE: 63W

COLOR TEMPERATURE: 5000K

METAL HALIDE EQUIVALENT: 250W

COLOR RENDERING INDEX (CRI): >80

WARRANTY: 5 Years

PRODUCT FEATURES

- Replacement for conventional metal halide lamp
- 50,000 + hour lifetime
- Environmentally friendly: No mercury used
- Instant startup
- UL listed
- DLC listed

RATED LIFE

L70 (Hours)

• Operating temperature: -29°C/-20°F to 60°C/140°F





- Integral driver, eliminates the need for external driver or ballast; includes 4kV surge protection
- IP64 rated; integrated heat sink quickly dissipates heat and guides water intrusion out of the lamp
- Suitable for use in fully enclosed fixture
- Do not use with standard dimmers. Not compatible with phase dimmers. Dimming functions with sensors only

OPERATING SPECIFICATIONS

ELECTRICAL CHARACTERISTICS

Input Voltage	Power Consumption	Power Factor	Input Current
120-277Vac	63W	>0.9	0.53A @ 120V 0.23A @ 277V

50.000

PHOTOMETRIC CHARACTERISTICS


Color Temperature (CCT)	5000K	
Luminous Flux*	9450 lm	
Color Rendering Index (CRI)	>80	
Efficacy	150 lm/W	
Visible Light Area	360º	
Based off of total lamp lumens		

SMART PORT



On the top of the lamp is a low-voltage AUX port for lamp level sensor controls which are coming soon, Q2+ 2019.

SPECTRAL DISTRIBUTION



LUX DISTANCE CURVE

	Flux Out: 886.3 Im	1	
		\wedge	
1 m "	282.1, 340.1 lx	Π.	200.00 cm
2 m ["]	70.53, 85.03 lx	\square	400.00 cm
3 m [°]	31.35, 37.79 lx		600.00 cm
4 m ["]	17.63, 21.26 lx		800.00 cm
5 m [°]	11.29, 13.61 lx		1000.00 cm
6 m [°]	7.837, 9.448 lx		1200.00 cm
7 m ["]	5.758, 6.941 lx		1400.00 cm
8 m [°]	4.408, 5.315 lx		1600.00 cm
9 m ["]	3.483, 4.199 lx		1800.00 cm
10 m ["]	2.821, 3.401 lx		2000.00 cm
Height	Eavg, Emax	Angle: 90º	Diameter

Keystone Technologies • Philadelphia, PA • Phone (800) 464-2680 • www.keystonetech.com Specifications subject to change. Last revised on 07.05.22





KT-LED63HID-EX39-850-D /G3 HID REPLACEMENT LED LAMP

SMART PORT LED



On the top of the lamp is a low-voltage AUX port for lamp level sensor controls.

SMART PORT LED AUX SENSORS



* For use with continuous dimming applications.

WIRING INSTRUCTIONS

STEP 1

Disconnect power. Disconnect and remove existing ballast, capacitor, and/or ignitor (where applicable) from fixture.


STEP 2

Rewire for line voltage to the lamp socket.

STEP 3

Install new LED replacement lamp. Ensure lamp is operating properly when power is turned on.











KT-LED63HID-EX39-850-D /G3 HID REPLACEMENT LED LAMP

PHYSICAL CHARACTERISTICS





LAMP DIMENSIONS

A (Illuminated Length)	5.66"	
B (Body Length)	10.40"	
C (Diameter)	3.34"	

BASE TYPE: EX39 (Mogul)

ORDERING INFORMATION

ORDER CODE	PACK QTY.	EASY CODE	UPC
KT-LED63HID-EX39-850-D/G3	16	PPJ-92	843654123172

CATALOG NUMBER BREAKDOWN

KT-LED63HID-EX39-850-D /G3

- **1** Keystone Technologies
- 2 LED Lamp
- 3 Wattage
- 4 Lamp Type
- 5 Base Type
- 6 800 Series
- 7 Color Temperature
- 8 Direct-Drive Series
- 9 Generation