



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ISPBS350 12AWG-350MCM Conn

Nsi Industries

Catalog Number	ISPBS350
Manufacturer	Nsi Industries
Description	Submersible Connector, #12 Awg Conductor Size, 350 MCM Conductor Size, Insulated, Epdm Rubber Insulation Material, Aluminum Conductor Material, Black Insulation Color, 2 Conductors, -45 °C Operating Temperature, +90 °C Operating Temperature, 8.83 In Overall Length, Screw Terminal, 600 V Ac, 0.62 LB/Ea
Weight per unit	0.6200 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Number of Conductors	2
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	350 MCM-12 AWG
Wire Type	Class B & C

Material, Color, and Finish

Color	Black
Finish	EPDM Rubber Insulated
Housing Material	Aluminum

Dimensions and Weight

Size	L=1.25 - W=8.83 - H=3.38
------	--------------------------

Descriptions

Description	12AWG-350MCM CONN
extra long description	NSI ISPBS350 Polaris Edge DB Connec
Features	The Polaris ISPBS350 2-Port In-Line Entry Submersible Connector provides the simplest solution for forming a secure connection between two conductors in direct burial or temporary submersal applications with a wide range of wire sizes. Sized for 350 MCM - 12 AWG wires and rated for 600V, this pre-insulated connector comes pre-loaded with an oxide inhibitor and installs faster than traditional connector options using just a hex key and torque wrench. The aluminum alloy body is wrapped in high-dielectric str

Manufacturer Information

GTIN	00662381787828
UPC	662381787828



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Submersible Pedestal Connectors

Packaging

Carton	3
Weight Per each	0.62

Uses, Certifications, and Standards

Application	Wire Termination
environmental conditions	90 C
standard	ANSI C119.4, C119.1, UL486D