



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

445 Texas Avenue
78664-2138, TX Round Rock
Phone: 512-246-8001
Fax: 512-246-8002



IT04 #4-#14 Polaris Insul-Tap Connector

Nsi Industries

Catalog Number	IT04
Manufacturer	Nsi Industries
Description	Insulation-Tap Connector, #14 Awg Conductor Size, #4 Awg Conductor Size, Insulated, Plastisol Insulation Material, Copper/Aluminum Conductor Material, Black Insulation Color, 2 Conductors, -45 °C Operating Temperature, +90 °C Operating Temperature, 1.12 In Overall Length, 600 V, 0.06 LB/Ea
Weight per unit	0.0600 (lbs/each)
Product Category	Large Terminals & Connectors

Descriptions

Description	#4-#14 POLARIS INSUL-TAP CONNECTOR
Features	The Polaris ITO-4 2-Port Offset Dual-Sided Connector provides the simplest solution for forming a secure connection between two conductors in applications including cable trays, panel boards, ducts, raceways or troughs. Sized for 4 - 14 AWG wires and rated for 600V, this pre-insulated connector comes pre-loaded with an oxide inhibitor and installs faster than traditional uninsulated connector options using just a hex key and torque wrench. The aluminum alloy body is wrapped in high-dielectric strength plas

Manufacturer Information

GTIN	00662381950024
UPC	662381950024

Taxonomies, Classifications, and Categories

Category Description	SPLIT BOLTS
----------------------	-------------

Packaging

Carton	12
Weight Per each	0.06