



## L710 4-In D/C Bushed Chase

*Topaz - Southwire LLC*

Catalog Number	L710
Manufacturer	Topaz - Southwire LLC
Description	Standard Hex Head Rigid Speed Nipple, Zinc Die-Cast, 1.47 In Length, Trade Size: 4 In, Flexibility: Rigid, Connection: Threaded, Width Across Flat: 5.15 In, Shelf Quantity: 5, Master Quantity: 20, UL Listed
Weight per unit	1.0 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

### Features

connection	Threaded
Material	Zinc Die-Cast

### Dimensions and Weight

Length	1.47
--------	------

### Descriptions

Description	4-IN D/C BUSHED CHASE
extra long description	SWC L-710 4 SPEED NIP
Long Description	STANDARD HEX HEAD RIGID SPEED NIPPLE, ZINC DIE-CAST, 1.47 IN LENGTH, TRADE SIZE: 4 IN, FLEXIBILITY: RIGID, CONNECTION: THREADED, WIDTH ACROSS FLAT: 5.15 IN, SHELF QUANTITY: 5, MASTER QUANTITY: 20, UL LISTED
Product Type	4 Speed Nip
Special Features	Serves as a short raceway between enclosures when used with a locknut

### Manufacturer Information

Brand	Madison Electric Products
GTIN	00784297350801
Manufacturers Part Number	L-710
UPC	784297350801

### Taxonomies, Classifications, and Categories

Category Description	COUPLINGS, ADAPTERS, REDUCERS, BUSHINGS, & CAPS
Type	Standard Hex Head Rigid Speed Nipple

### Trade Size

Trade Size	4
------------	---

### Packaging

Carton	1
Weight Per each	1



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

8620 E 34th St N  
67226-0000, KS Wichita  
Phone: 316-247-8220  
Fax: 000-000-0000

## Uses, Certifications, and Standards

Application

Serves as a short raceway between enclosures when used with a locknut

standard

UL Listed