



## 20 AMP NEMA L820 SINGLE RECEPTACLE

L820R | [Pass & Seymour](#)

### FEATURES & BENEFITS

Industrial Spec Grade SingleTurnlok 20amp 480V Receptacle



- Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.
- Face color coding by voltage facilitates locating and mating of proper devices.
- One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.
- Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.
- Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.
- Side and external screw-pressure-plate back wire capability.
- Accepts #14 - #10 AWG.

### SPECIFICATIONS

#### GENERAL INFO

Type: Single Receptacles

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Standard: Yes  
CUL Listing No: No  
cURus: No  
Federal Spec: No  
UL Listing No: 498  
UL Standard: Yes  
UN SPSC: 39121403  
UR: No

#### DIMENSIONS

Depth (US): 1.19"  
Height (US): 3.28"  
Width (US): 1.61"

#### TECHNICAL INFORMATION

Amps: 20A  
NEMA Configuration Number: L820

#### BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant





## 20 AMP NEMA L820 SINGLE RECEPTACLE

L820R | [Pass & Seymour](#)

### FEATURES & BENEFITS

Industrial Spec Grade SingleTurnlok 20amp 480V Receptacle



- Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.
- Face color coding by voltage facilitates locating and mating of proper devices.
- One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.
- Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.
- Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.
- Side and external screw-pressure-plate back wire capability.
- Accepts #14 - #10 AWG.

### SPECIFICATIONS

#### GENERAL INFO

Type: Single Receptacles

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Standard: Yes  
CUL Listing No: No  
cURus: No  
Federal Spec: No  
UL Listing No: 498  
UL Standard: Yes  
UN SPSC: 39121403  
UR: No

#### DIMENSIONS

Depth (US): 1.19"  
Height (US): 3.28"  
Width (US): 1.61"

#### TECHNICAL INFORMATION

Amps: 20A  
NEMA Configuration Number: L820

#### BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant

