



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

8420 Tejas Loop
78045-0000, TX Laredo
Phone: 956-462-0607
Fax: 956-284-6601



ITG6 #6-#14 Polaris Insul-Tap Connector For Dlo Cable

Nsi Industries

Catalog Number	ITG6
Manufacturer	Nsi Industries
Description	Multi-Tap Connector, #14 Awg Conductor Size, #6 Awg Conductor Size, Insulated, Plastisol Insulation Material, Copper Conductor Material, Gray Insulation Color, 2 Conductors, -45 °C Operating Temperature, +90 °C Operating Temperature, 1.13 In Overall Length, 600 V Ac, 0.06 LB/Ea
Weight per unit	0.0600 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Number of Conductors	2
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	(Class B,C,D) 6-14 AWG - (Class K,M,I) 6-14 AWG
Wire Type	B,C,D,K,M,I

Material, Color, and Finish

Color	Gray
Finish	Plastisol Insulated
Housing Material	Aluminum

Dimensions and Weight

Size	L=1.130 - W=1.240 - H=1.370
------	-----------------------------

Descriptions

Description	#6-#14 POLARIS INSUL-TAP CONNECTOR FOR DLO CABLE
extra long description	NSI ITG-6 POLARIS Grey Multi-Tap 6
Features	<p>The Polaris ITG-6 2-Port Single-Side Connector provides the simplest solution for forming a secure connection between two fine-stranded wire conductors in applications including cable trays, troughs, wire-ways, raceways, ducts and motor junction boxes. Sized for 6 - 14 AWG wires and rated for 600V, this pre-insulated connector comes pre-loaded with an oxide inhibitor and installs faster than traditional uninsulated connector options using just a hex key and torque wrench. The aluminum alloy body is wrapped</p>

Manufacturer Information

GTIN	00662381951403
UPC	662381951403



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

8420 Tejas Loop
78045-0000, TX Laredo
Phone: 956-462-0607
Fax: 956-284-6601

Taxonomies, Classifications, and Categories

Category Description	SPLIT BOLTS
Type	Multi Cable

Packaging

Carton	3
Package	12
Weight Per each	0.06

Uses, Certifications, and Standards

Application	Wire Termination
environmental conditions	90 C
standard	UL 486A/B